



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™

WIRE FERL UNINSUL

Non-Insulated Wire Ferrules



Image
Unavailable

Cat No: 77/15VZ

UPC No: 783310050339

Description

- For terminating stranded wire into terminal blocks
- Electrolytic copper and tin plating provide maximum conductivity and low contact resistance
- Meets DIN 46228, part 1, 0.5 - 50 mm²

Specifications

- Color Code : DIN 46228, Part 1
- Finish : Tin Plated
- Material : Electrolytic Copper
- Recommended Crimping Tools : K28GL, K34GL, Die 03283
- Size : 0.591 IN (15.000 MM) Overall Length
- Standard : RoHS
- Type : Non Insulated
- Wire Size : 6 AWG (16.000 SQ-MM)
- Wire Type : Stranded