




MATERIALS:

Retractable Sheath Banana Plug:

Plug Body: Brass, Nickel Plated.

Banana Plug Spring: Beryllium Copper.

Compression Spring: Stainless Steel

Tip: Nylon, Color Matches Color of Wire.

Insulation: Nylon Molded to the Plug Body and Wire. Color Matches Color of Wire.

Wire: 18 AWG, Stranding 65 x 36 t.c., PVC Insulated, .144 (3,66cm) O.D.

Marking: POMONA 5259-XX

Color: Referenced by Part Number.

In-Line Banana Jack:

Jack Body: Brass, Nickel Plated.

Insulation: Polypropylene Molded to the Jack Body and Wire. Color Matches Color of wire.

Marking: POMONA ELECTRONICS CALIF.

RATINGS:

Operating Temperature: +55°C (+131°F) Max.

Operating Voltage: 1000 VRMS.

Operating Current: 10 Amperes Max.

ORDERING INFORMATION: Model 5259-XX-*

XX = Wire Length, Standard Lengths: 12" (30,48cm), 24" (60,96cm), 36" (91,44cm), 48" (121,92cm) & 60" (152,4cm). Additional lengths can be quoted upon request.

* = Color, -0 Black, -2 Red

Ordering Example: 5259-12-2 Patch Cord is 12" (30,48cm), Color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5259-12-2](#) [5259-12-0](#) [5259-36-0](#) [5259-36-2](#) [5259-24-0](#) [5259-24-2](#) [5259-48-0](#) [5259-48-2](#)