



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/3/03	DFP
B	ECN 3206: UPDATE DWG FORMAT	2/29/08	D.GRIFFIN
C	ECN5761: UL STYLE WAS 2725. UPDATED PACKAGING NOTE & DWG FORMAT. UPDATED PICTORALLY.	10/11/11	DFP



WIRING DIAGRAM

NOTES:

CABLE:
FLAT CABLE, UL21149
TWO 26 AWG PAIRS SHIELDED AND DRAIN WIRE
INSULATOR MATERIAL: FM-PE
COLOR: RED
IMPEDANCE: 100 $\Omega \pm 10$


CONNECTOR:
INSULATOR: UL94V-0 RATED
COLOR: BLACK
CONTACTS: PHOSPHOR BRONZE
PLATING: 15 μ INCHES GOLD
OVERMOLD: PVC
COLOR: BLACK

PACKAGING:
INDIVIDUALLY PACKAGE IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

NOTE:
1. CABLE IS WIRED STRAIGHT THROUGH
2. BOTH SHIELDS AND ALL DRAIN WIRES TIED TOGETHER.

TABLE		
MODEL	METERS	FEET
CASATAR-05M	0.5	1.64
CASATAR-1M	1	3.28

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. PARHAM	04/02/2003		
	CHECKED BY T. CLARK	04/03/2003	CATEGORY HETEROGENOUS	
	APPROVED BY C. McCORMICK	04/03/2003	PRODUCT DESCRIPTION SERIAL ATA CABLE	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
COLOR VARIATIONS MAY OCCUR		DWG. NO. CASATAR	REV. B1	SCALE: NONE
		CAD FILE: CASATAR.SLDDRW	SHEET 1 OF 1	