

TORXPlus®

For Improved Torque and Longer Tool Life


Not for use in standard
Torx fasteners


361 TORXPlus® L-key, Short Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
361 06	IP6	39	1.5	16	.6	.01	10
361 07	IP7	42	1.7	16	.6	.01	10
361 08	IP8	45	1.8	16	.6	.01	10
361 09	IP9	48	1.9	16	.6	.01	10
361 10	IP10	51	2.0	17	.7	.01	10
361 15	IP15	55	2.2	19	.7	.01	10
361 20	IP20	58	2.3	19	.7	.01	10
361 25	IP25	63	2.5	21	.8	.01	10
361 27	IP27	68	2.7	22	.9	.02	10
361 30	IP30	73	2.9	24	.9	.03	10
361 40	IP40	81	3.2	26	1.0	.05	10



361 97 TORXPlus® L-key, Short Arm 7 Pc. Set In Holder

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item No.	lbs.	pkg.	Set includes the following L-keys:
361 97	.10	1	IP6, IP7, IP8, IP9, IP10, IP15, IP20



361 99 TORXPlus® L-key, Short Arm 9 Pc. Set In Holder

Set includes the following L-keys:

Item No.	lbs.	pkg.	Set includes the following L-keys:
361 99	.30	1	IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40


Not for use in standard
Torx fasteners


366 TORXPlus® L-key, Long Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
366 06	IP6	64	2.5	14	.6	.01	10
366 07	IP7	68	2.7	14	.6	.01	10
366 08	IP8	74	2.9	15	.6	.01	10
366 09	IP9	78	3.1	16	.6	.01	10
366 10	IP10	83	3.3	18	.7	.01	10
366 15	IP15	88	3.5	18	.7	.02	10
366 20	IP20	94	3.7	18	.7	.02	10
366 25	IP25	98	3.9	19	.7	.03	10
366 27	IP27	107	4.2	23	.9	.05	10
366 30	IP30	114	4.5	24	.9	.06	10
366 40	IP40	118	4.6	27	1.0	.09	10



366 90 TORXPlus® L-key, Long Arm 7 Pc. Set In Holder

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item No.	lbs.	pkg.	Set includes the following L-keys:
366 90	.22	1	IP6, IP7, IP8, IP9, IP10, IP15, IP20



366 91 TORXPlus® L-key, Long Arm 9 Pc. Set In Holder

Set includes the following L-keys:

Item No.	lbs.	pkg.	Set includes the following L-keys:
366 91	.35	1	IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40

[See TorxPlus® Fold-Ups On Page 28](#)