

Product Data Sheet


Part No. WST-1212S Washable Type

(self drive circuit)



φ 12 × H9.5

DIMENSIONS



UNIT : mm
TOLERANCE : ±0.3
HOUSING MATERIAL : PBT

Type	Unit	
Color		Black
Rated Voltage	(V)	12
Operating Voltage	(V)	8-16
Current Consumption	(mA)	MAX.30
Sound Output (Min)	(dB)	85
Resonance Frequency	(Hz)	2300±200
Operating Temp	(C)	-20~+60
Storage Temp	(C)	-30~+70
Weight	(g)	2
Terminal		PIN TYPE
Dimension	mm	12 x H9.5
*applied voltage: rated voltage (DC)		
*distance for measurement 10cm		

CHARACTERISTICS

