




SKINTOP® MS-M

Versatile brass cable gland

Approval
UL 50 Type 6
UL 514 B



Application

Cable gland with metric thread according to EN 50262 suitable for a wide range of applications from manufacturing machinery and plant engineering to measurement and control equipment, medical equipment and other areas with high requirement for stability and safety.

Note

Suitable accessories see from [[976]].

Technical Data

 Material: Körper: Messing vernickelt Einsatz: Polyamid Dichtring: CR/NBR O-Ring: NBR	 Temperature range: -30°C bis +100°C	 Protection class: IP 68 - 5 bar	Attention Einbaumaße und Anzugsdrehmomente siehe T21
---	---	---	--

Part-Number	Thread size M	Clamping range mm	Wrench Size mm	C mm	D mm	PU pieces
-------------	---------------	-------------------	----------------	------	------	-----------

For a quotation please click on a part number

SKINTOP® MS-M

5311 2000	12 x 1,5	3 - 7	16	26,5	6,5	100
5311 2010	16 x 1,5	4,5 - 10	20	32	7	100
5311 2020	20 x 1,5	7 - 13	24	35,5	8	50
5311 2030	25 x 1,5	9 - 17	29	37,5	8	25
5311 2040	32 x 1,5	11 - 21	36	42,2	9	25
5311 2050	40 x 1,5	19 - 28	45	49,5	9	10
5311 2060	50 x 1,5	27 - 35	54	52	10	5
5311 2070	63 x 1,5	34 - 45	67	61,3	15	5