


Data Sheet

Sucoflex Assemblies

Description

ID (Product Code)	22648916
Description (Product)	SF104/11SMA/11N47/1000mm



Product Configuration

Cable	SUCOFLEX_104
Connector A	SF_11_SMA-451
Connector B	SF_11_N-47

Technical Data

Electrical Data

Impedance	50 Ω
Operating Frequency	0.018 to 18 GHz
Min. Return Loss	≥ 18 dB
Max. Attenuation	1.39 dB
Frequency range (GHz)	0.018 to 18
Return loss (dB)	≥ 18
Max. Attenuation	1.39
Max. VSWR	1.29

Mechanical Data

Weight	0.11 kg
Length REF/REF	1000 mm ± mm
Min. Bending Radius repeated	25 mm
Max. Tensile Force	250 N

Environmental Data

Operating Temperature	-65 °C to + 125 °C
Waterproof	IP65
2011/65/EU (RoHS)	not compliant