

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19


© COPYRIGHT 19

BY TE INCORPORATED.

ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
AF	50				H3	ECR-15-005665	10AUG15	BDA/PKS

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS.
- 2 SLOT ACCEPTS 0.36–0.57 mm [#27–#23] AWG COPPER MAGNET WIRE.
SLOT ACCEPTS 0.51–0.64mm [#24–#22] ALUMINUM MAGNET WIRE.
ALUMINUM WIRE RANGE APPLIES FOR POST-TIN PLATED VERSIONS ONLY.
- 3 MATES WITH STANDARD MAG-MATE STYLED POKE-IN TAB TERMINAL.
- 4 0.002032 [.000080] MIN TIN OVER 0.00127 [.000050] MIN NICKEL.
- 5 TIN PLATE



		H04 PHOS. BRONZE	1-63551-3
		1-63551-3	63551-3
OBSOLETE		4M BRASS	63551-2
OBSOLETE		4M BRASS	63551-1
	FINISH	MATERIAL	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± 0.25 [.010] ANGLES ± -	DR 8/21/89 MICHAEL S. FEHER	 TE Connectivity	
	CHK 8/23/89 JR RUTH		
MATERIAL SEE TABLE	APPD 8/23/89 DF DECKER	NAME SPECIAL LEAF CONTACT, 300 SERIES MAG-MATE™	
	APPD 8/23/89 TL SHUTTER		
FINISH SEE TABLE	PRODUCT SPEC 108-2012	SIZE B	CAGE CODE 00779
	APPLICATION SPEC 114-2046	DRAWING NO 63551	
	WEIGHT —	SCALE 5:1	SHEET 1 OF 1

METRIC