



Order Code

MHRJ - 45 - 8P8C - R - 30

Series _____
 Type _____
 RJ-22, RJ-11, RJ-12, RJ-45, RJ-48
 Size and Contacts _____
 4P4C (RJ22), 6P4C (RJ11), 6P6C (RJ12),
 6P6C-OST (RJ12), 8P8C (RJ45),
 10P10C (RJ48)
 Cable Style _____
 F = Flat or Oval, R = Round
 Plating Options _____
 Omit = 50u"
 6 = 6u", 15 = 15u", 30 = 30u"



Order Code


RJ45SRB - QR - R

Strain Relief Boot _____
 Omit = Bubble Boot (Anti Snag) _____
 QR = Quick Release
 Colour _____
 LG = Grey, BK = Black, R = Red,
 G = Green, BL = Blue, Y = Yellow


- Compatible with all FCC specifications
- 50µ" gold plated contacts as standard, but also available in 6, 15 and 30u" plating

- UL94V-0 polycarbonate body
- True knife blade, insulating piercing contacts
- Compatible with standard crimping tools


Four Conductor/Four Position Handset Cord Plug Flat Cable Entry




Four Conductor/Six Position Line Cord Plug Round Cable Entry



Six Conductor/Six Position Line Cord Plug Round Cable Entry



Eight Conductor/Eight Position Patch Cable Plug Round Cable Entry



Ten Conductor/ Ten Position

