






CONTACT LAYOUT



NOTES:

- 1 MATERIAL HOUSING : GREY GLASSFILLED POLYESTER
CONTACT : COPPER ALLOY
- 2 GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN.
AND ACTION PIN: 0,5µm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR
EACH DASH NUMBER.
- 3 CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101 PERFORMANCE LEVEL 2.
4 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III,
CENTRAL OFFICE APPLICATIONS.
- 5 CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.
- 6 CONNECTOR MARKED WITH PARTNUMBER AND DATECODE
- 7 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.
- 8 HOLES IN ROW f POSSIBLE FUTURE USE OF
GROUND RETURN SHIELDS. (NOT YET TOOLED)
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 10 0,76µm MIN. GOLD PLATING AT MATING SURFACES.

9 OBSOLETE	  	3-352406-0
	  	352406-9
	 	352406-1
	CONTACT FINISH	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.V.d.HEIJDEN CHK D. TRUREN 21MAR98 21MAR98		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLCS $\pm$ ANGLES $\pm$ ±0.20			
MATERIAL 		FINISH SEE TABLE DWN F.V.KONINGSBRUGGE PRODUCT SPEC 108-19082 APPLICATION SPEC 114-19029 WEIGHT —		NAME Z-PACK 2MM HM TYPE B19 95 POS. RIGHT ANGLE MALE CONNECTOR ASSEMBLY SIZE A2 CAGE CODE 00779 DRAWING NO C-352406 RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE NTS SHEET 1 of 1 REV F	