



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS


DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
811	C	Renamed - was CHC-**	JWM	8/28/05	JC	9/14/01	JC	9/14/01
1865	D	RoHS ADDED	DCM	10/17/05	JWM	10/18/05	JWM	10/18/05



RoHS
Compliant

PART NO.	HOLDING DIA. RANGE	THICKNESS "T"	WIDTH "W"
CHC-19	17/32-19/32(13.5-15.0)	.07 (1.8)	.22 (5.6)
CHC-21	19/32-21/32(15.0-16.7)		
CHC-28	3/4-7/8 (19.1-22.2)		
CHC-32	7/8-1 (22.2-25.4)		
CHC-35	61/64-1-3/32 (24.2-27.8)		.31 (7.9)
CHC-38	1-1/32-1-3/16 (26.2-30.1)		
CHC-52	1-13/32-1-5/8 (37.5-41.3)		.36 (9.1)
CHC-58	1-19/32-1-13/16(40.5-46.0)		



NOTES:

1. MATERIAL: NYLON 6/6
2. COLOR: WHITE
3. FLAMMABILITY RATING: UL94V-2

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
Tolerances: Unless
Otherwise Specified:
.XX = ± 0.10
.XXX = ± 0.005
Fractional = $\pm 1/64$
Angles = $\pm 1^\circ$

DRAWN BY:

JAP

DATE:

3/19/93

CHECKED BY:

JC

DATE:

3/23/93

APPROVED BY:

JL

DATE:

3/23/93

DRAWING TITLE:

Snap-It Hose Clamps

SIZE

A

DWG. NO.

TA-399

ELECTRONIC FILE

TA-399.dwg

REV

D

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1