




REVISION AB

DO NOT SCALE
FROM THIS PRINT




* PIN ALIGNMENT REFERENCE TO -S-SM OPTION ONLY
SEE NOTE 5



AVAILABLE ON 8 - 40 POSITION ONLY

"N" = USE MEASURED DIMENSION
"Q" = {("N" - .400 [10.16]) / 2} ± .020 [.51]



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
ELECTRONIC OR MECHANICAL,
INCLUDING PHOTOCOPYING,
RECORDING, OR BY ANY
INFORMATION STORAGE AND
RETRIEVAL SYSTEM, WITHOUT
THE WRITTEN CONSENT OF SAMTEC INC.

DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED		TOLERANCES ARE:	ANGLES ± 2°	TITLE:	DWG NO:
ONE PLACE DECIMALS ± .1 [2.5]	THREE PLACE DECIMALS ± .005 [.13]			HI-TEMP TERMINAL MICRO-STRIP(SINGLE ROW)	FTR-1XX-XX-XX-S-XX-XX
TWO PLACE DECIMALS ± .01 [.25]	FOUR PLACE DECIMALS ± .0020 [.051]				SHEET 1 OF 1

FTR-1XX-XX-XX-S-XX-XX

BODY LENGTH SPEC
EXPRESSED IN # POS PER ROW
(-02 THRU -40)
"A" = "XX" x .050 [1.27]

LEAD STYLE SPEC
SEE TABLE 1

PLATING SPECIFICATION

- G: GOLD (USE T-1M6-XX-G-2)
- T: TIN (USE T-1M6-XX-T-2)
- S: SELECTIVE GOLD (USE T-1M6-XX-S-2)
- F: FLASH SELECTIVE GOLD (USE T-1M6-XX-F-2)
(LEAD STYLE SPEC -01 ONLY)
- TM: TIN MATTE (USE T-1M6-XX-T-2)
- FM: FLASH SELECTIVE GOLD/MATTE TIN TAIL (USE T-1M6-XX-F-2)
- SM: SELECTIVE GOLD/MATTE TIN TAIL (USE T-1M6-XX-S-2)

BODY SPECIFICATION

- S: SINGLE (USE HTMS-50-S)

OPTION

- P: PICK & PLACE PAD
(USE PPP-11)
- TR: TAPE & REEL
(4 POS MIN)

OPTION

- POLARIZING SPECIFICATION
(XX INDICATES POS. TO BE OMITTED)

NOTES:

1. MAX ALLOWABLE BOW: .005 INCH/INCH.
2. TERMINAL PUSHOUT FORCE: 2 lbs. MIN.
3. MAX PIN ROTATION IN BODY: 2°.
4. SHEAR TAIL TO DIMENSION GIVEN.
5. NOTE DELETED.
6. Ⓢ REPRESENTS A CRITICAL DIMENSION
FOR STATISTICAL PROCESS CONTROL USE.
7. TUBE POSITIONS -05 THRU -50 ONLY FOR THIS
LEAD STYLE.
8. .003 [.08] MAX BURR
9. CUT FLASH: .010 [.25] MAX

TABLE 1

LEAD STYLE	TERMINAL SPEC.	"B"	TUBE (SEE NOTE 7)	PLUG
-01	T-1M6-13-X-2	.230 [5.84]	PT-1-24-01-46	TP-24
-01 (W/PAD OPTION)	T-1M6-13-X-2	.230 [5.84]	PT-1-24-05-29	TP-03
-02	T-1M6-04-X-2	.100 [2.54]	PT-1-24-02-29	TP-24
-02 (W/PAD OPTION)	T-1M6-04-X-2	.100 [2.54]	PT-1-24-05-29	TP-03
-03 (W/PAD OPTION)	T-1M6-04-X-2	.125 [3.18]	PT-1-24-04-15	TP-09
-03 (NO OPTIONS)	T-1M6-04-X-2	.125 [3.18]	PT-1-24-02-29	TP-24
-21	N/A	.230 [5.84]	N/A	N/A
-51	T-1M6-13-X-2	.190 [4.83]	PT-1-24-02-29	TP-24
-52	T-1M6-13-X-2	.205 [5.21]	PT-1-24-13-29	TP-24
-52 (W/PAD OPTION)	T-1M6-13-X-2	.205 [5.21]	PT-1-24-05-29	TP-03
-53	T-1M6-05-X-2	.285 [7.24]	PT-1-24-02-29	TP-24
-54	T-1M6-15-X-2	.335 [8.51]	PT-1-24-13-29	TP-24
-55	T-1M6-16-X-2	.390 [9.91]	PT-1-24-10-29	TP-24
-56	T-1M6-16-X-2	.405 [10.29]	PT-1-24-10-29	TP-24
-57	T-1M6-16-X-2	.430 [10.92]	PT-1-24-03-71	TP-24
-58	N/A	.485 [12.32]	N/A	N/A
-59	N/A	.535 [13.59]	N/A	N/A
-60	N/A	.605 [15.37]	N/A	N/A
-53,-54,-55,-56,-57 (W/PAD OPTION)	N/A	N/A	PT-1-24-03-71	TP-09

TABLE 2

LENGTH	"L"
-04	.505 [12.83]
-05	.705 [17.91]
-13	.625 [15.88]
-15	.755 [19.18]
-16	.825 [20.96]

MATERIAL:
BODY:
LIQUID CRYSTAL POLYMER
COLOR: BLACK
TERMINAL:
PHOS BRONZE
MAX FLASH ALLOWED:
.004 [.10]
MAX GATE VESTIGE
ALLOWED: .002 [.05]

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47151-1147
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:
BRATCHER 7-10-95

FTR-1XX-XX-XX-S-XX-XX
SHEET 1 OF 1