


AUTO LINK PAL FUSES - 294

RoHS



Description

PAL fuses are commonly found on many Japanese and domestic built vehicles.

Specifications

Voltage Rating: 32 VDC
Current Cycling: 24°C
The fuses satisfy the performance requirements after 50% of the rated current is applied for 10,000 cycles. Each cycle consists of an interrupted current with the pattern of 5 minutes ON and 10 minutes OFF.
Operating Temperature Range: -40°C to +125°C

Complies with JASO 0612

Ordering Information

Part Number	Package Size
0294xxx.H	100
0294xxx.U	500
0294xxx.MXJ	1000

Time-Current Characteristics


% of Rating	Opening Time Min / Max (s)
110	14,400 s
200	5 s / 100 s
350	0.2s / 7 s
600	0.040 s / 1 s

Ratings

Part Number	Current Rating (A)	Body Color
0294030._	30	PINK
0294040._	40	GREEN
0294050._	50	RED
0294060._	60	YELLOW
0294070._	70	BROWN
0294080._	80	BLACK
0294100._	100	BLUE
0294120._	120	WHITE

Dimensions

Dimensions in mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[0294120.T](#) [0294030.U](#) [0294040.MXJ](#) [0294050.HXJ-C](#) [0294120.HXJ-C](#) [0294030.MXJ-C](#) [0294030.H](#) [0294040.H](#)
[0294030.T](#) [0294060.T](#) [0294050.MXJ-C](#) [0294040.T](#) [0294080.H](#) [0294070.U](#) [0294100.T](#) [0294070.HXJ-C](#)
[0294030.MXJ](#) [0294060.MXJ](#) [0294080.MXJ-C](#) [0294060.MXJ-C](#) [0294050.H](#) [0294120.U](#) [0294060.H](#) [0294070.MXJ](#)
[0294120.MXJ](#) [0294070.T](#) [0294040.MXJ-C](#) [0294050.T](#) [0294040.U](#) [0294050.U](#) [0294030.HXJ-C](#) [0294100.MXJ-C](#)
[0294080.HXJ-C](#) [0294050.MXJ](#) [0294080.MXJ](#) [0294080.U](#) [0294100.H](#) [0294120.H](#) [0294100.U](#) [0294070.H](#)
[0294040.HXJ-C](#) [0294100.HXJ-C](#) [0294120.MXJ-C](#) [0294080.T](#) [0294060.U](#) [0294070.MXJ-C](#) [0294060.HXJ-C](#)
[0294100.MXJ](#)