

D.C. MILLI-OHM METER



GOM-801H




FEATURES

- * Measures from 20mΩ ~ 20kΩ in 7 Ranges
- * 1A High Test Current
- * High Resolution 10 μΩ
- * Hi/Lo Comparator Indicator and Buzz Alarm
- * 3 1/2 Digits 0.5" LED Display

GTL-108A Test Lead

For: GOM-801H/802 , GDM-8255A/8251A



The GOM-801H milliohm meter is the ideal device for quick and precise component and material resistance measurements. The main display is equipped with a 3 1/2 digit 0.5" red LED with comparator indicators. Measurable objects can cover cable joints, earth bonds, switches, motors, transformers and generators. The front panel features seven selectable test ranges, 20mΩ to 20kΩ. The internal comparator is fully adjustable for the user settable Hi/Lo comparison indicator. The GOM-801H is the best choice for an inexpensive, easy to use, yet reliable milliohm meter.

SPECIFICATIONS	
TEST RANGE	
	20, 200m , 2, 20, 200 , 2k, 20k , 7 Ranges
TEST CURRENT (Test Voltage 0.2V)	
	20m /200m : 1A 2 : 0.1A 20 : 10mA 200 : 1mA 2k : 100μA 20k : 10μA
ACCURACY	
Measuring	20m ± (0.2% rdg + 6 digits) 200m ~ 20k ± (0.2% rdg + 4 digits)
Setting	± (0.2% + 6 digits)
RESOLUTION	
	0.01 , 0.1 , 1 , 10 , (≥ symbol) 100m , 1 , 10
COMPARATOR	
	HI, LO settable
DISPLAY	
	3 1/2 digits 0.5" LED display HI, GO, LO indicator
POWER SOURCE	
AC 100V/120V/220V/230V±10% , 50/60Hz	
DIMENSIONS & WEIGHT	
230(W) x 95(H)x280(D)mm, Approx. 2 kg	

ORDERING INFORMATION	
GOM-801H	High Precision Programmable DC Milli-Ohm Meter
ACCESSORIES :	
User manual x 1 , Power cord x 1	
Test Lead GTL-108A x 1	