





LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
CM	53											S2	REDRAWN PER STANDARDS	5-26-87	51/RS		
												S3	REVISED PER ECO-09-026346	27NOV09	KK	AEG	



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1



SECTION C-C
SCALE 10:1

- 1. PLATED INSIDE WITH .000030 GOLD OVER .000050 NICKEL UNDERPLATE.
- 2. REELED FOR MINI-APPLICATOR.
- 3. WIRE RANGE: 26-18 AWG
INSULATION RANGE: .050-.115 DIA.
- 4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

PART NUMBER	MATERIAL	FINISH
350665-1	.008 PHOS. BRONZE	PRE-TIN
350665-2	.008 PHOS. BRONZE	PRE-GOLD STRIPE

4 OBSOLETE

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON 2 PL DEC ± 3 PL DEC ± .010 ANGLES ±		DR <i>S. James</i> 5-26-87 CHK <i>R. Spring</i> 6-1-87 APPD <i>W. S. Jensen</i> 6-2-87 APPD		PART NO	
MATERIAL SEE TABLE		PRODUCT SPEC		NAME MR RECEPACLE	
FINISH SEE TABLE		APPLICATION SPEC		DRAWING NO 350665	
WEIGHT		SCALE 5:1		SHEET 1 OF 1	

CUSTOMER DRAWING