



0237 - Series 5x20mm Designed to UL/CSA Standards Medium Acting Fuse

Part No.	Rating	Part No.	Rating
0237001.	1A	0237004.	4A
02371.25	1.25A	0237005.	5A
023701.6	1.6A	0237006.	6A
0237002.	2A	023706.3	6.3A
023702.5	2.5A	0237008.	8A
0237003.	3A	0237010.	10A
02373.15	3.15		



For Full Part number, please reference packaging and version specifications

Electrical Characteristics (UL248 Part 14 – Supplemental Fuses)

Rated Current	1.0 In	1.35 In		2 In		4 In		10 In	
	MIN	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
1A – 6A	4	3	1	400	2.25	80	300	10	40
6.3A – 10A	1	3	1	400	2.25	80	300	10	40
	h	s	h	ms	s	ms	ms	ms	ms


Voltage Rating 125V ac.

Interrupting Rating(UL) 1A – 10A 10000A @ 125V ac 0.7-0.8 power factor.

Approvals

Agency Approvals			Ampere Range	
	Certificate No.	Cartridge NBK280602-E10480 C NBK290502-E10480 I	1A – 5A	125V 10000A
		Leaded NBK280602-E10480 D NBK290502-E10480 J	6A – 10A	125V 500A
	Listed File No.	E10480	1A – 10A	
	Guide No.	JDYX		
	File No.	029862		
	Certified Class No.	LR1422-01		

Dimensions



Materials

Body	Glass
Cap	Nickel Plated Brass
Lead	Tin Plated Copper

Rating	Element Type
1A – 2.5A	Corrugated
3A – 10A	Straight