


OPERATING CHARACTERISTICS AT T_A = 25 C°

SYMBOL	PARAMETER	LED COLOR (DIFFUSED)	MIN	TYP	MAX	UNITS	TEST COND.
V _F	FORWARD VOLTAGE	YELLOW		1.9	2.7	V	I _F = 2 mA
		GREEN		1.8	2.2		
λ _{PK}	PEAK WAVELENGTH	YELLOW		583		nm	MEASURED AT PEAK
		GREEN		565			
I _V	LUMINOUS INTENSITY	YELLOW	1.0	1.6		mcd	I _F = 2 mA
		GREEN	1.0	1.6			



B	_____	ADDED SLOTS ON TOP OF HOUSING FOR LED LEADS BENDING. ADDED .020X45° CHFR. REF. FOR STANDOFF.		η, θ.	11-2-94
A	_____	NEW RELEASE		N.O.	10-21-94
LTR	ECN NO.	REVISIONS		APP.	DATE
THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE PRIOR WRITTEN CONSENT OF DIALIGHT.					
SCALE	DRAWN	DATE	CUSTOMER DRAWING NO.		DWG. REV.
4:1	DC	10-20-94	C-15913		B
TOLERANCES: UNLESS OTHERWISE SPECIFIED ALL DIM'S IN: <u>INCHES</u> MM			TITLE		
FRACTIONS: ± 1/64 DECIMALS(.XX) ± .020 DECIMALS(.XXX) ± .015 ANGLES ± 3°			PART NUMBER 551-0006-801		
FINISH:			DIALIGHT CORPORATION 1913 Atlantic Ave. Manasquan, NJ 08736		
FSCM 83330					