






| LOC | DIST | REVISONS |     |                           |         |            |
|-----|------|----------|-----|---------------------------|---------|------------|
|     |      | P        | LTR | DESCRIPTION               | DATE    | DWN I APVD |
| GP  | 00   | C        |     | REVISED PER ECO-08-004045 | 26MAR08 | JDP SLB    |




- 1 NO SNAP-IN POLARIZING FEATURE ON THIS END FOR 10 & 14 POS. HEADERS.
- 2 POSTS: GOLD FLASH OVER PALLADIUM-NICKEL PLATE, .000030 MIN TOTAL ON THE LOCALIZED PLATE AREA, .000100 MIN TIN PLATE ON THE SOLDER-TAIL, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE POST.  
-OR-  
.000030 MIN GOLD PLATE ON THE LOCALIZED PLATE AREA, .000100 MIN TIN PLATE ON THE SOLDER-TAIL, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
- 3 RECOMMENDED STENCIL THICKNESS EQUALS .010
- 4 FOR 10 POS HEADER ONLY, ONE SLOT LOCATED AS SHOWN.
- 5 MOLDED PARTS: FLAME RETARDANT PCT, UL94V-0 RATED, COLOR RED.  
POSTS: PHOS BRONZE OR BRASS.



RECOMMENDED  
P C BOARD MOUNTING DIMENSIONS

|          |       |       |       |      |      |            |             |
|----------|-------|-------|-------|------|------|------------|-------------|
|          | 3.100 | 3.400 | 3.560 | 3.80 | 3.96 | 64         | 1-5111008-2 |
|          | 2.900 | 3.200 | 3.360 | 3.60 | 3.76 | 60         | 1-5111008-1 |
|          | 2.400 | 2.700 | 2.860 | 3.10 | 3.26 | 50         | 1-5111008-0 |
|          | 1.900 | 2.200 | 2.360 | 2.60 | 2.76 | 40         | 5111008-9   |
|          | 1.600 | 1.900 | 2.060 | 2.30 | 2.46 | 34         | 5111008-8   |
|          | 1.400 | 1.700 | 1.860 | 2.10 | 2.26 | 30         | 5111008-7   |
| OBSOLETE | 1.200 | 1.500 | 1.660 | 1.90 | 2.06 | 26         | 5111008-6   |
|          | 1.100 | 1.400 | 1.560 | 1.80 | 1.96 | 24         | 5111008-5   |
| OBSOLETE | .900  | 1.200 | 1.360 | 1.60 | 1.76 | 20         | 5111008-4   |
| OBSOLETE | .700  | 1.000 | 1.160 | 1.40 | 1.56 | 16         | 5111008-3   |
| OBSOLETE | .600  | .900  | 1.060 | 1.30 | 1.46 | 14         | 5111008-2   |
|          | .400  | .700  | .860  | 1.10 | 1.26 | 10         | 5111008-1   |
|          | E     | D     | C     | B    | A    | NO OF POSN | PART NO     |

|                                                                                                   |  |                                                                                                 |  |                              |                                                           |  |                    |                        |                    |                 |
|---------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------|--|------------------------------|-----------------------------------------------------------|--|--------------------|------------------------|--------------------|-----------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                            |  |                                                                                                 |  | DWN<br>C. ATTADIA - 01-07-05 | Tyco Electronics Corporation<br>Harrisburg, PA 17105-3608 |  |                    |                        |                    |                 |
| DIMENSIONS:<br>INCHES                                                                             |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                                       |  | CHK<br>S. BOLASH - 01-07-05  | NAME<br>M. WALMSLEY - 01-07-05                            |  |                    |                        |                    |                 |
|              |  | PLC<br>±                                                                                        |  | PRODUCT SPEC<br>108-40018    |                                                           |  |                    |                        |                    |                 |
|                                                                                                   |  | PLC<br>±                                                                                        |  | APPLICATION SPEC             |                                                           |  |                    |                        |                    |                 |
|                                                                                                   |  | PLC<br>± .005                                                                                   |  |                              |                                                           |  |                    |                        |                    |                 |
|                                                                                                   |  | PLC<br>±                                                                                        |  |                              |                                                           |  |                    |                        |                    |                 |
|                                                                                                   |  | ANGLES<br>±                                                                                     |  | SIZE<br>A1                   |                                                           |  | CAGE CODE<br>00779 | DRAWING NO<br>C5111008 | RESTRICTED TO<br>— |                 |
| MATERIAL<br> |  | FINISH<br> |  | WEIGHT<br>—                  |                                                           |  | CUSTOMER DRAWING   |                        | SCALE<br>4:1       | SHEET<br>1 OF 1 |