

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

[130124-0057](#)

Status:

Active

Description:

Pow-R-Feed® Transfer Trumpet Guide




image - Reference only

Series

EU RoHS

China RoHS

RoHS Compliance

Not Required

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130124Series](#)

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Conductor Bars
Series	130124
Component Type	Transfer Guide
Current - Max. per Conductor	N/A
Depth	51.40mm (2.024")
Duty	Standard
Height	86.25mm (3.400")
Product Name	Pow-R-Feed
UPC	78678866164
Woodhead	Yes

Physical	
Material - Housing	N/A
Material - Metal	N/A
Material - Resin	ABS
Material - Wheel	N/A
Net Weight	999.990/kg
Packaging Type	Individual Carton
Temperature Range - Operating	-30°C to +60°C

Electrical	
Voltage - Maximum	600V

Material Info	
Old Part Number	AITN7