





LFM (with T1 3/4 LED) IP 67

Models	Dimensions	Frontpanel drilling
Internal reflector  with built-in resistor  without built-in resistor 		
Outside reflector  with built-in resistor  without built-in resistor 		

Technical data

1. Electrical data

Current input	10 mA With built-in resistor
Technical data LED 0925.0059/60/61 see p.100/101	

2. Other data

Solderability	max. 2s 235 °C (IEC 68 2-20 Test Ta Method 1)
Soldering heat resistance	max. 5s 350 °C (IEC 68 2-20 Test Tb Method 1B)
Ambient temperature	-25°C ... +55°C
Storage temperature	-55°C ... +100°C
Degree of protection	IP 67

3. Materials

Body	Brass chromium-plated
Solder Terminals	Copper tinned
Nut	Brass nickel-plated
Sealing	Nitril rubber

4. Mounting type

Frontpanel mounting with solder terminals

Internal reflector LFM (with T13/4 LED) IP 67

Models	Variations	select your colour	Part Number
with built-in resistor		Colour of LED	
		12V	<p>red <input type="checkbox"/> 0035.0604</p> <p>green <input type="checkbox"/> 0035.0605</p> <p>yellow <input type="checkbox"/> 0035.0606</p>
	Body chrome plated	24V	<p>red <input type="checkbox"/> 0035.0607</p> <p>green <input type="checkbox"/> 0035.0608</p> <p>yellow <input type="checkbox"/> 0035.0609</p>
with built-in resistor		Colour of LED	
		12V	<p>red <input type="checkbox"/> 0035.0644</p> <p>green <input type="checkbox"/> 0035.0645</p> <p>yellow <input type="checkbox"/> 0035.0646</p>
	Body black dull	24V	<p>red <input type="checkbox"/> 0035.0647</p> <p>green <input type="checkbox"/> 0035.0648</p> <p>yellow <input type="checkbox"/> 0035.0649</p>
without built-in resistor	Body chrome plated	Colour of LED	<p>red <input type="checkbox"/> 0035.0721</p> <p>green <input type="checkbox"/> 0035.0722</p> <p>yellow <input type="checkbox"/> 0035.0723</p>
without built-in resistor	Body black dull	Colour of LED	<p>red <input type="checkbox"/> 0035.0726</p> <p>green <input type="checkbox"/> 0035.0727</p> <p>yellow <input type="checkbox"/> 0035.0728</p>
Accessories	Spring lock washer		<input type="checkbox"/> 0638.1004

Outside reflector LFM (with T1 3/4 LED) IP 67

Models	Variations			select your colour	Part Number
with built-in resistor			Colour of LED		
		12V	red	<input type="checkbox"/>	0035.0624
	Body chrome plated		green	<input type="checkbox"/>	0035.0625
			yellow	<input type="checkbox"/>	0035.0626
		24V	red	<input type="checkbox"/>	0035.0627
			green	<input type="checkbox"/>	0035.0628
			yellow	<input type="checkbox"/>	0035.0629
with built-in resistor			Colour of LED		
		12V	red	<input type="checkbox"/>	0035.0664
	Body black dull		green	<input type="checkbox"/>	0035.0665
			yellow	<input type="checkbox"/>	0035.0666
		24V	red	<input type="checkbox"/>	0035.0667
			green	<input type="checkbox"/>	0035.0668
			yellow	<input type="checkbox"/>	0035.0669
without built-in resistor	Body chrome plated	Colour of LED	red	<input type="checkbox"/>	0035.0731
			green	<input type="checkbox"/>	0035.0732
			yellow	<input type="checkbox"/>	0035.0733
without built-in resistor	Body black dull	Colour of LED	red	<input type="checkbox"/>	0035.0736
			green	<input type="checkbox"/>	0035.0737
			yellow	<input type="checkbox"/>	0035.0738
Accessories	Spring lock washer			<input type="checkbox"/>	0638.1004