



- Robust aluminium enclosure for mechanical engineering and automation technology
- Fixing options for DIN rails and mounting plates
- Usable in wide temperature area

Technical Data

Material:

DIN EN 1706 EN AC-AISI 12 (Fe)

Painting:

powder coating

Colour:

RAL 7001, silver grey

special colour on request

Ingress protection:

IP 66 to EN 60529

higher protection on request

Impact resistance:

7 Joule to EN 60079-0

Temperature range:

PU (polyurethane) seal (std.): -40°C to +90°C

CR (chloroprene) seal: -40°C to +100°C

VMQ(silicone) seal (optional): -60°C to +130°C

Included in delivery

Aluminium enclosure consisting of lid, seal incl. captive +/- stainless steel screws, base with 2 or 4 earthing screws

Aluminium Standard

Programme range

Standard enclosures

Order No.	W x L x H (mm)	DIN rails for terminals		Earthing rail, number of clamps	Mounting plate, thickness in mm ¹⁾	External brackets set ²⁾	External aluminium hinge pair ^{3), 4)}	Internal hinge pair ^{2), 4)}	Quick lock ⁵⁾	Turn bolt fastener ⁴⁾
		TS 15	TS 35							
01.05 05 03	45 x 50 x 30									
01.06 06 03	64 x 58 x 34									
01.06 10 03	64 x 98 x 34									
01.06 15 03	64 x 150 x 34									
01.06 19 03	64 x 185 x 34									
01.08 08 06	80 x 75 x 57				1,5					
01.08 13 06	80 x 125 x 57				1,5					
01.08 18 06	80 x 175 x 57				1,5					
01.08 25 05	80 x 250 x 52									
01.10 10 08	100 x 100 x 81				1,5					
01.10 16 08	100 x 160 x 81				1,5					
01.10 20 08	100 x 200 x 81				1,5					
01.12 12 08	120 x 122 x 81			6	1,5					
01.12 12 09	120 x 122 x 91			6	1,5					
01.12 22 08	120 x 220 x 81			13	1,5					
01.12 22 09	120 x 220 x 91			13	1,5					
01.12 22 12	120 x 220 x 118			13	1,5					
01.12 36 08	120 x 360 x 81			23	1,5					
01.14 14 09	140 x 140 x 91			6	1,5					
01.14 20 09	140 x 200 x 91			11	1,5					
01.16 16 09	160 x 160 x 91			8	1,5					
01.16 26 09	160 x 260 x 91			16	1,5					
01.16 36 09	160 x 360 x 91			23	1,5					
01.16 56 09	160 x 560 x 91			36	2,0					
01.18 18 10	180 x 180 x 101			8	1,5					
01.18 28 10	180 x 280 x 101			17	1,5					
01.23 10 11	230 x 100 x 111			-	1,5					
01.23 20 11	232 x 202 x 111			10	1,5					
01.23 20 18	232 x 202 x 181			10	1,5					
01.23 28 11	230 x 280 x 111			16	1,5					
01.23 33 11	230 x 330 x 111			21	1,5					
01.23 33 18	230 x 330 x 181			21	1,5					
01.23 40 11	230 x 400 x 111			25	2					
01.23 40 23	230 x 400 x 225			25	2					
01.23 60 11	230 x 600 x 111			40	2					
01.31 40 11	313 x 404 x 111			25	2					
01.31 40 14	312 x 403 x 141			25	2					
01.31 40 18	313 x 404 x 181			25	2					
01.31 40 23	313 x 404 x 227			25	2					
01.31 60 11	310 x 600 x 111			40	2					
01.31 60 18	310 x 600 x 181			40	2					
01.60 60 20	600 x 600 x 202				2,5					

Field enclosure with integrated external fastening

01.06 12 00	64 x 115 x 34
01.06 19 00	64 x 185 x 34

¹⁾ galvanized sheet steel ²⁾ stainless steel ³⁾ diecast alu ⁴⁾ Please quote installation side A-D when ordering ⁵⁾ on request

Other accessories

EMC screening (without type 01.60 60 20)

SWB/SBG/SBGL corrosion protection (RAL 5009)

Allen lid screws (without type 01.60 60 20)

Silicone lid seal up to +130°C

Sealable lid screws in steel (without type 01.60 60 20)

Terminal mounting

Phoenix																Earth conductor connection																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			
DIN rail TS 15	X	X	X													MSLKG 5 insulated, green/yellow USLKG 1.5 N insulated green/yellow USLKG 2.5 N insulated green/yellow USLKG 6 N insulated green/yellow USLKG 10 N insulated green/yellow USLKG 16 N insulated green/yellow USLKG 3 insulated green/yellow USLKG 5 insulated green/yellow USLKG 50 insulated green/yellow USLKG 95 insulated green/yellow																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			

* 2 DIN rails possible = double number of terminals
 ** 3 DIN rails possible = triple number of terminals

Aluminium Standard

Terminal mounting

Weidmüller																				Earth conductor connection				
DIN rail TS 15					X	X	X	X													WPE	Earthing bar 2.5 mm² with cable lug max. 10 mm²	Earthing screw M4 with cable lug max. 6 mm²	M6 with cable lug max. 35 mm²
DIN rail TS 35									X	X	X	X	X	X	X	X	X	X	X					
Voltage (V)	500	400	400	400	250	400	250	400	500	800	800	800	1000	1000	1000	1000	1000	1000	1000	1000				
Current (A)	24	32	32	32	17	15	24	32	24	24	32	41	57	76	125	192	232	269	309	415				
Nom. cross section (mm²)	2,5	4	4	4	1,5	1,5	2,5	4	2,5	2,5	4	6	10	16	35	70	95	120	150	240				
Terminal width (mm)	38	38	52	92	5,1	3,5	5,1	6,1	5,1	5,1	6,1	8	10	12	16	20,5	27	27	32	36				
Terminal type																								
Type	MK 3/4 (4-pole)	BK 4 (4-pole)	BK 6 (6-pole)	BK 12 (12-pole)	AKZ 1.5	WDU 1,5 / R 3.5	AKZ 2.5	AKZ 4	WDU 2,5 N	WDU 2,5	WDU 4	WDU 6	WDU 10	WDU 16	WDU 35	WDU 70 N	WDU 70 / 95	WDU 95 / 120 N	WDU 120 / 150	WDU 240				
01.05 05 03	1																							
01.06 06 03		1																						
01.06 10 03			1																					
01.06 15 03				1																				
01.06 19 03				1																				
01.08 08 06					8	11	8	6	8															
01.08 13 06					18	26	18	15	18															
01.08 18 06					28	40	28	23	28															
01.08 25 05					43	61	43	36	43															
01.10 10 08					13	18	13	10	13															
01.10 16 08					25	36	25	21	25															
01.10 20 08					33	47	33	27	33															
01.12 12 08										16	13	10												
01.12 12 09										16	13	10	8									5		
01.12 22 08										35	29	22	17									13	4	
01.12 22 09										35	29	22	17									13	4	
01.12 22 12										36	30	22	18									13	4	
01.12 36 08										63	52	39	31									23	4	
01.14 14 09										20	16	12	10									6	4	
01.14 20 09										32	26	20	16	13								11	4	
01.16 16 09										23	19	14	11	9								8	4	
01.16 26 09										43	36	27	21	18								16	4	
01.16 36 09										63	52	39	31	26								23	4	
01.16 56 09										103	86	64	51	43								38	4	
01.18 18 10										28	23	17	14	11								8	4	
01.18 28 10										47	39	29	23	19								17	4	
01.23 10 11											31	23	18	15								13	4	
01.23 20 11										32*	26*	20*	16*	13*	10	7						12	4	
01.23 20 18										32*	26*	20*	16*	13*	10	7						12	4	
01.23 28 11										47*	39*	29*	23*	19*	14	11						16	4	
01.23 33 11										57*	48*	36*	28*	24*	18	14						21	4	
01.23 33 18										57*	48*	36*	28*	24*	18	14						21	4	
01.23 40 11										71*	59*	44*	35*	29*	22*	17						25	4	
01.23 40 23										71*	59*	44*	35*	29*	22*	17	13	13				25	4	
01.23 60 11										111*	92*	69*	55*	46*	34*	27						41	4	
01.31 40 11										71**	59**	44**	35**	29**	22*	17						26	4	
01.31 40 14										71**	59**	44**	35**	29**	22*	17						26	4	
01.31 40 18										71**	59**	44**	35**	29**	22*	17	13	13				26	4	
01.31 40 23										71**	59**	44**	35**	29**	22*	17	13	13				26	4	
01.31 60 11										111**	92**	69**	55**	46**	34*	27						40	4	
01.31 60 18										111**	92**	69**	55**	46**	34*	27	20	20				40	4	
01.60 60 20										109**	91**	68**	54**	45**	34**	26**	20**	20**	15	15		40	4	
Field enclosure with integrated external fastening																								
01.06 12 00			1																					
01.06 19 00				1																				

* 2 DIN rails possible = double number of terminals

** 3 DIN rails possible = triple number of terminals


Accessories




External brackets
set = 4 pcs

Order No.	for enclosure
10.03 11 01	01.08 08 06 - 01.10 20 08
10.03 11 02	01.12 12 08 - 01.31 60 18

Type 10.03 11 01




Type 10.03 11 02



External hinge
opening angle 150°
set = 2 pcs

Order No. **10.02 70 01**





Internal hinge
opening angle 95°
set = 2 pcs

Order No. **10.02 20 01**



Weight: **91 g**

	DIN rail length in mm
	max. fitting length in mm
	Earthing rail clamp
	Mounting plate (thickness in mm)
	External mounting brackets
	External hinge* set
•	EMC version
	Internal hinge* set
•	SWB / SBG / SBGL Corr.protection
•	Allen lid screws
	Silicone lid seal
•	Sealable lid screws in steel
	Turn bolt fastener on request
	Quick lock

Maximum number of
cable glands **to DIN 50262***



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	2	1	7	17.25	2	1
16	25.30			9	21.85	1	
20	27.60			11	25.30		
25	37.95			13.5	27.60		
32	48.30			16	31.05		
40	60.95			21	37.95		
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		



Type: **01.06 06 03**

External dimensions: **64 x 58 x 34 mm**



Weight: **165 g**

	DIN rail length in mm
	max. fitting length in mm
	Earthing rail clamp
	Mounting plate (thickness in mm)
	External mounting brackets
	External hinge* set
•	EMC version
	Internal hinge* set
•	SWB / SBG / SBGL Corr.protection
•	Allen lid screws
•	Silicone lid seal
•	Sealable lid screws in steel
	Turn bolt fastener on request
	Quick lock

Maximum number of
cable glands **to DIN 50262***



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	2	1	7	17.25	2	1
16	25.30			9	21.85	1	1
20	27.60			11	25.30		
25	37.95			13.5	27.60		
32	48.30			16	31.05		
40	60.95			21	37.95		
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		

* Please quote mounting side

Weight: **224 g**

[illegible]

Maximum number of
cable glands *to DIN 50262**


A

C


D

B

M	Corner dim.	Side		PG	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	4	1	7	17.25	4	1
16	25.30			9	21.85	3	1
20	27.60			11	25.30		
25	37.95			13.5	27.60		
32	48.30			16	31.05		
40	60.95			21	37.95		
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688




Type: **01.06 12 00**

External dimensions: **64 x 115 x 34 mm**


Weight: **290 g**

	DIN rail length in mm
	max. fitting length in mm
	Earthing rail clamp
	Mounting plate (thickness in mm)
	External mounting brackets
	External hinge* set
•	EMC version
	Internal hinge* set
•	SWB / SBG / SBGL Corr.protection
•	Allen lid screws
•	Silicone lid seal
•	Sealable lid screws in steel
	Turn bolt fastener on request
	Quick lock

Maximum number of cable glands to DIN 50262*							
A C D B							
<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	5	1	7	17.25	5	1
16	25.30			9	21.85	4	1
20	27.60			11	25.30		
25	37.95			13.5	27.60		
32	48.30			16	31.05		
40	60.95			21	37.95		
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		




* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



* Please quote mounting side

Type: **01.06 15 03**External dimensions: **64 x 150 x 34 mm**Weight: **316 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 15													
139						•		•	•	•	•		



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688

Cylinder screw
M4x20/7
similar to DIN 84


Maximum number of
cable glands **to DIN 50262***



M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	8	1	7	17.25	8	1
16	25.30			9	21.85	6	1
20	27.60			11	25.30		
25	37.95			13.5	27.60		
32	48.30			16	31.05		
40	60.95			21	37.95		
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		

Type: **01.06 19 03**External dimensions: **64 x 185 x 34 mm**Weight: **500 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 15													
174						•		•	•	•	•		



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688

Cylinder screw
M4x20/7
similar to DIN 84

Maximum number of
cable glands **to DIN 50262***




M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	10		7	17.25	10	
16	25.30			9	21.85		
20	27.60			11	25.30		
25	37.95			13.5	27.60		
32	48.30			16	31.05		
40	60.95			21	37.95		
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		

* Please quote mounting side


Type: **01.06 19 00**External dimensions: **64 x 185 x 34 mm**Weight: **420 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 15													
174						•		•	•	•	•		

Maximum number of cable glands to DIN 50262*							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
		B	D			B	D
12	17.25	10	1	7	17.25	10	1
16	25.30			9	21.85	7	1
20	27.60			11	25.30		
25	37.95			13.5	27.60		
32	48.30			16	31.05		
40	60.95			21	37.95		
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		




* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688


Type: **01.08 08 06**External dimensions: **80 x 75 x 57 mm**Weight: **360 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 15													
63	46		1.5	•		•		•	•	•	•		•

Maximum number of cable glands to DIN 50262*							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
		B	D			B	D
12	17.25	3	5	7	17.25	2	5
16	25.30	1	2	9	21.85	1	2
20	27.60	1	2	11	25.30	1	2
25	37.95	1	1	13.5	27.60	1	2
32	48.30			16	31.05	1	1
40	60.95			21	37.95		
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



* Please quote mounting side


Weight: **500 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 15													
113	96		1.5	•		•		•	•		•		•


Maximum number of
cable glands **to DIN 50262***




Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Base



<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	9	5	7	17.25	8	5
16	25.30	4	2	9	21.85	6	2
20	27.60	3	2	11	25.30	3	2
25	37.95	2	1	13.5	27.60	3	2
32	48.30			16	31.05	2	1
40	60.95			21	37.95	2	
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		


Type: **01.08 18 06**

External dimensions: **80 x 175 x 57 mm**


Weight: **630 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 15													
163	146		1.5	•		•		•	•	•	•		•


Maximum number of
cable glands **to DIN 50262***




Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Base




<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	14	5	7	17.25	14	5
16	25.30	6	2	9	21.85	9	2
20	27.60	5	2	11	25.30	6	2
25	37.95	3	1	13.5	27.60	5	2
32	48.30			16	31.05	4	1
40	60.95			21	37.95	3	
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		

* Please quote mounting side

Type: **01.08 25 05**External dimensions: **80 x 250 x 52 mm**Weight: **818 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 15													
238	220			•		•		•	•	•	•		•

Maximum number of cable glands to DIN 50262*							
							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	23	6	7	17.25	22	6
16	25.30	9	2	9	21.85	15	3
20	27.60	8	2	11	25.30	9	2
25	37.95	5	1	13.5	27.60	8	2
32	48.30			16	31.05	6	1
40	60.95			21	37.95	5	1
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		

Type: **01.10 10 08**External dimensions: **100 x 100 x 81 mm**Weight: **800 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 15/35													
87,5	70		1.5	•	•	•		•	•	•	•		•

Maximum number of cable glands to DIN 50262*							
							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	12	9	7	17.25	12	9
16	25.30	6	4	9	21.85	8	5
20	27.60	5	3	11	25.30	5	4
25	37.95	2	1	13.5	27.60	5	3
32	48.30	1	1	16	31.05	4	2
40	60.95			21	37.95	2	1
50	69.00			29	48.30	1	1
63	74.75			36	60.95		
				42	69.00		
				48	74.75		




* Please quote mounting side

Weight: **870 g**


Maximum number of
cable glands ***to DIN 50262****

<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	24	9	7	17.25	22	8
16	25.30	11	4	9	21.85	17	5
20	27.60	10	3	11	25.30	11	4
25	37.95	4	1	13.5	27.60	10	3
32	48.30	3	1	16	31.05	8	2
40	60.95			21	37.95	4	1
50	69.00			29	48.30	3	1
63	74.75			36	60.95		
				42	69.00		
				48	74.75		



Weight: **1200 g**

Maximum number of cable glands <i>to DIN 50262*</i>							
A C B D							
<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	32	9	7	17.25	30	9
16	25.30	14	4	9	21.85	21	5
20	27.60	12	3	11	25.30	12	4
25	37.95	5	1	13.5	27.60	12	3
32	48.30	3	1	16	31.05	10	2
40	60.95			21	37.95	5	1
50	69.00			29	48.30	3	1
63	74.75			36	60.95		
				42	69.00		
				48	74.75		




30

Type: **01.12 12 08**External dimensions: **120 x 122 x 81 mm**Weight: **1044 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
107	85	5	1.5	•	•	•		•	•	•	•		•


Maximum number of cable glands to DIN 50262*							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
		B	D			B	D
12	17.25	10	11	7	17.25	10	11
16	25.30	5	5	9	21.85	8	6
20	27.60	4	4	11	25.30	5	4
25	37.95	2	2	13.5	27.60	4	3
32	48.30	1	1	16	31.05	3	2
40	60.95			21	37.95	2	2
50	69.00			29	48.30	2	1
63	74.75			36	60.95		
				42	69.00		
				48	74.75		

Lid




* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688

Cylinder screw
M6x25/10
similar to DIN 84




Base

Type: **01.12 12 09**External dimensions: **120 x 122 x 91 mm**Weight: **1170 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
107	85	5	1.5	•	•	•		•	•	•	•		•


Maximum number of cable glands to DIN 50262*							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
		B	D			B	D
12	17.25	10	11	7	17.25	10	11
16	25.30	5	5	9	21.85	8	6
20	27.60	4	4	11	25.30	5	4
25	37.95	2	2	13.5	27.60	4	3
32	48.30	1	1	16	31.05	3	2
40	60.95			21	37.95	2	2
50	69.00			29	48.30	1	1
63	74.75			36	60.95		
				42	69.00		
				48	74.75		

Lid




* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688

Cylinder screw
M6x25/10
similar to DIN 84



Base




* Please quote mounting side


Type: **01.12 22 08**External dimensions: **120 x 220 x 81 mm**Weight: **1445 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
205	183	13	1.5	•	•	•		•	•	•	•		•


Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688




Base



Cylinder screw
M6x25/10
similar to DIN 84

Top
4

Maximum number of
cable glands **to DIN 50262***




M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	30	11	7	17.25	30	11
16	25.30	12	6	9	21.85	20	6
20	27.60	12	4	11	25.30	12	4
25	37.95	5	2	13.5	27.60	12	4
32	48.30	3	1	16	31.05	10	2
40	60.95			21	37.95	5	2
50	69.00			29	48.30	3	1
63	74.75			36	60.95		
				42	69.00		
				48	74.75		


Type: **01.12 22 09**External dimensions: **120 x 220 x 91 mm**Weight: **1800 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
205	183	13	1.5	•	•	•		•	•	•	•		•


Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688




Base



Cylinder screw
M6x35/10
similar to DIN 84

Top
4

Maximum number of
cable glands **to DIN 50262***



M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	34	11	7	17.25	34	11
16	25.30	15	6	9	21.85	24	6
20	27.60	14	4	11	25.30	15	4
25	37.95	6	2	13.5	27.60	14	4
32	48.30	4	1	16	31.05	11	2
40	60.95			21	37.95	6	2
50	69.00			29	48.30	4	1
63	74.75			36	60.95		
				42	69.00		
				48	74.75		


* Please quote mounting side

Type: **01.12 22 12**External dimensions: **120 x 220 x 118 mm**Weight: **1410 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
208	183	13	1.5	•	•	•		•	•	•	•		•

Maximum number of cable glands to DIN 50262*							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
		B	D			B	D
12	17.25	34	11	7	17.25	34	11
16	25.30	15	6	9	21.85	24	6
20	27.60	14	4	11	25.30	15	4
25	37.95	6	2	13.5	27.60	14	4
32	48.30	4	1	16	31.05	11	2
40	60.95			21	37.95	6	2
50	69.00			29	48.30	4	1
63	74.75			36	60.95		
				42	69.00		
				48	74.75		


Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688




Base

Type: **01.12 36 08**External dimensions: **120 x 360 x 81 mm**Weight: **2100 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
343	323	23	1.5	•	•	•		•	•	•	•		•

Maximum number of cable glands to DIN 50262*							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
		B	D			B	D
12	17.25	58	11	7	17.25	58	11
16	25.30	26	5	9	21.85	41	6
20	27.60	24	4	11	25.30	26	4
25	37.95	10	2	13.5	27.60	24	3
32	48.30	7	1	16	31.05	20	2
40	60.95			21	37.95	10	2
50	69.00			29	48.30	7	1
63	74.75			36	60.95		
				42	69.00		
				48	74.75		


Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Base




* Please quote mounting side


Weight: **1760 g**

[illegible]


Maximum number of
cable glands **to DIN 50262***




Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Base



<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	26	16	7	17.25	26	16
16	25.30	12	8	9	21.85	15	11
20	27.60	9	6	11	25.30	12	6
25	37.95	5	3	13.5	27.60	9	6
32	48.30	3	2	16	31.05	8	5
40	60.95	2	1	21	37.95	5	3
50	69.00	2		29	48.30	2	2
63	74.75			36	60.95	2	1
				42	69.00	1	
				48	74.75		


Type: **01.16 26 09**

External dimensions: **160 x 260 x 91 mm**


Weight: **2300 g**

[illegible]


Maximum number of
cable glands **to DIN 50262***




Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Base




<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	50	16	7	17.25	50	16
16	25.30	24	8	9	21.85	30	11
20	27.60	17	6	11	25.30	23	6
25	37.95	10	3	13.5	27.60	17	6
32	48.30	5	2	16	31.05	14	5
40	60.95	3	1	21	37.95	9	3
50	69.00	3		29	48.30	5	2
63	74.75			36	60.95	3	1
				42	69.00	3	
				48	74.75		

* Please quote mounting side

Type: **01.16 36 09**External dimensions: **160 x 360 x 91 mm**Weight: **2940 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
343	320	23	1.5	•	•	•	•	•	•	•	•	•	•



Maximum number of cable glands to DIN 50262*									
M	Corner dim.	Side		PG	Corner dim.	Side			
		A	C			A	C		
12	17.25	72	16	7	17.25	72	16		
16	25.30	36	8	9	21.85	42	11		
20	27.60	24	6	11	25.30	33	6		
25	37.95	15	3	13.5	27.60	24	6		
32	48.30	7	2	16	31.05	20	5		
40	60.95	5	1	21	37.95	14	3		
50	69.00	4		29	48.30	7	2		
63	74.75			36	60.95	5	1		
				42	69.00	4			
				48	74.75				

Type: **01.16 56 09**External dimensions: **160 x 560 x 91 mm**Weight: **4457 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
543	520	38	2	•	•	•	•	•	•	•	•	•	•




Maximum number of cable glands to DIN 50262*									
M	Corner dim.	Side		PG	Corner dim.	Side			
		A	C			A	C		
12	17.25	104	16	7	17.25	104	16		
16	25.30	58	8	9	21.85	66	11		
20	27.60	40	6	11	25.30	58	6		
25	37.95	24	3	13.5	27.60	40	6		
32	48.30	12	2	16	31.05	32	5		
40	60.95	8	1	21	37.95	24	3		
50	69.00	6		29	48.30	12	2		
63	74.75			36	60.95	8	1		
				42	69.00	6			
				48	74.75				

* Please quote mounting side


Type: **01.18 18 10**External dimensions: **180 x 180 x 101 mm**Weight: **2400 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
166	140	8	1.5	•	•	•	•	•	•	•	•	•	•



Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Base


Maximum number of cable glands **to DIN 50262***

M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
		B	D			B	D
12	17.25	30	20	7	17.25	28	20
16	25.30	15	9	9	21.85	18	14
20	27.60	11	8	11	25.30	15	8
25	37.95	6	3	13.5	27.60	11	8
32	48.30	3	2	16	31.05	8	6
40	60.95	2	2	21	37.95	6	3
50	69.00	2		29	48.30	3	2
63	74.75			36	60.95	2	2
				42	69.00	2	
				48	74.75		


Type: **01.18 28 10**External dimensions: **180 x 280 x 101 mm**Weight: **3000 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
264	240	16	1.5	•	•	•	•	•	•	•	•	•	•


Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Base

Maximum number of cable glands **to DIN 50262***



M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
		B	D			B	D
12	17.25	52	22	7	17.25	52	22
16	25.30	26	10	9	21.85	33	15
20	27.60	18	8	11	25.30	23	10
25	37.95	11	4	13.5	27.60	18	8
32	48.30	5	2	16	31.05	14	7
40	60.95	4	2	21	37.95	10	4
50	69.00	3		29	48.30	5	2
63	74.75			36	60.95	4	2
				42	69.00	3	
				48	74.75		

* Please quote mounting side

Type: **01.23 10 11**External dimensions: **230 x 100 x 111 mm**Weight: **2300 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
214	190		1.5	•	•	•	•	•	•	•	•	•	•

Lid



Base

* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Maximum number of cable glands **to DIN 50262***

M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	15	45	7	17.25	15	45
16	25.30	8	18	9	21.85	10	28
20	27.60	6	17	11	25.30	6	18
25	37.95	3	8	13.5	27.60	6	17
32	48.30	2	5	16	31.05	5	12
40	60.95	1	3	21	37.95	3	8
50	69.00	1	2	29	48.30	1	4
63	74.75		2	36	60.95	1	3
				42	69.00	1	2
				48	74.75	1	2

Type: **01.23 20 11**External dimensions: **232 x 202 x 111 mm**Weight: **2880 g**



DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
186	160	12	1.5	•	•	•	•	•	•	•	•	•	•

Lid



Base

* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688

Maximum number of cable glands **to DIN 50262***

M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	45	45	7	17.25	45	45
16	25.30	22	18	9	21.85	28	28
20	27.60	18	17	11	25.30	20	18
25	37.95	8	8	13.5	27.60	18	17
32	48.30	6	5	16	31.05	15	12
40	60.95	3	3	21	37.95	8	8
50	69.00	2	2	29	48.30	5	4
63	74.75	2	2	36	60.95	3	3
				42	69.00	2	2
				48	74.75	2	2


* Please quote mounting side

Type: **01.23 20 18**External dimensions: **232 x 202 x 181 mm**Weight: **4600 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
186	160	12	1.5	•	•	•	•	•	•	•	•	•	•


Maximum number of cable glands to DIN 50262*							
							
<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A	C			A	C
12	17.25	90	81	7	17.25	90	81
16	25.30	42	36	9	21.85	56	49
20	27.60	33	33	11	25.30	42	36
25	37.95	18	16	13.5	27.60	33	33
32	48.30	10	9	16	31.05	25	25
40	60.95	6	6	21	37.95	16	16
50	69.00	5	5	29	48.30	10	9
63	74.75	4	4	36	60.95	6	5
				42	69.00	5	4
				48	74.75	4	4

Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688

Cylinder screw
M6x25/10
similar to DIN 84




Base

Type: **01.23 28 11**External dimensions: **230 x 280 x 111 mm**Weight: **3460 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
264	240	16	1.5	•	•	•	•	•	•	•	•	•	•


Maximum number of cable glands to DIN 50262*							
							
<i>M</i>	Corner dim.	Side		<i>PG</i>	Corner dim.	Side	
		A	C			A	C
12	17.25	70	45	7	17.25	68	45
16	25.30	32	18	9	21.85	44	28
20	27.60	24	17	11	25.30	32	18
25	37.95	12	8	13.5	27.60	24	17
32	48.30	9	5	16	31.05	21	12
40	60.95	4	3	21	37.95	12	8
50	69.00	3	2	29	48.30	9	4
63	74.75	3	2	36	60.95	4	3
				42	69.00	3	2
				48	74.75	3	2

Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688

Cylinder screw
M6x25/10
similar to DIN 84




Base

* Please quote mounting side

Type: **01.23 33 11**External dimensions: **230 x 330 x 111 mm**Weight: **3500 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
314	290	21	1.5	•	•	•	•	•	•	•	•	•	•



Maximum number of cable glands to DIN 50262*							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	84	45	7	17.25	81	45
16	25.30	42	18	9	21.85	52	28
20	27.60	30	17	11	25.30	38	18
25	37.95	15	8	13.5	27.60	30	17
32	48.30	11	5	16	31.05	27	12
40	60.95	5	3	21	37.95	15	8
50	69.00	4	2	29	48.30	11	4
63	74.75	4	2	36	60.95	5	3
				42	69.00	4	2
				48	74.75	4	2

Type: **01.23 33 18**External dimensions: **230 x 330 x 181 mm**Weight: **6400 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
314	290	21	1.5	•	•	•	•	•	•	•	•	•	•



Maximum number of cable glands to DIN 50262*							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	165	81	7	17.25	144	81
16	25.30	77	36	9	21.85	104	49
20	27.60	60	33	11	25.30	77	36
25	37.95	30	16	13.5	27.60	60	33
32	48.30	18	9	16	31.05	45	25
40	60.95	11	6	21	37.95	30	16
50	69.00	8	5	29	48.30	18	9
63	74.75	8	4	36	60.95	11	5
				42	69.00	8	4
				48	74.75	8	4


* Please quote mounting side

Type: **01.23 40 11**External dimensions: **230 x 400 x 111 mm**Weight: **4833 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
381	360	26	2	•	•	•	•	•	•	•	•	•	•

Maximum number of cable glands to DIN 50262*							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
		B	D			B	D
12	17.25	103	45	7	17.25	103	45
16	25.30	50	18	9	21.85	64	28
20	27.60	39	17	11	25.30	46	18
25	37.95	20	8	13.5	27.60	39	17
32	48.30	14	5	16	31.05	33	12
40	60.95	6	3	21	37.95	18	8
50	69.00	5	2	29	48.30	13	4
63	74.75	5	2	36	60.95	6	3
				42	69.00	5	2
				48	74.75	5	2


Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Base



Cylinder screw
M6x25/10
similar to DIN 84


Top

Type: **01.23 40 23**External dimensions: **230 x 400 x 225 mm**Weight: **8300 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
381	360	26	2	•	•	•	•	•	•	•	•	•	•

Maximum number of cable glands to DIN 50262*							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
		B	D			B	D
12	17.25	240	108	7	17.25	240	108
16	25.30	122	48	9	21.85	160	63
20	27.60	100	44	11	25.30	112	48
25	37.95	54	21	13.5	27.60	100	44
32	48.30	30	13	16	31.05	77	35
40	60.95	18	9	21	37.95	54	21
50	69.00	15	6	29	48.30	30	13
63	74.75	12	5	36	60.95	18	6
				42	69.00	15	6
				48	74.75	12	5


Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Base



Cylinder screw
M6x25/10
similar to DIN 84

Top

* Please quote mounting side

Type:


01.23 60 11

External dimensions: **230 x 600 x 111 mm**

Weight: **8700 g**

[illegible]

Maximum number of cable glands to DIN 50262*								
A C B D								
M	Corner dim.	Side		PG	Corner dim.	Side		
		A B	C D			A B	C D	
12	17.25	150	43	7	17.25	150	43	
16	25.30	72	18	9	21.85	96	28	
20	27.60	54	17	11	25.30	68	18	
25	37.95	28	8	13.5	27.60	54	15	
32	48.30	20	4	16	31.05	28	12	
40	60.95	10	3	21	37.95	28	8	
50	69.00	8	2	29	48.30	20	4	
63	74.75	6	2	36	60.95	10	2	
				42	69.00	8	2	
				48	74.75	6	2	



Type:


01.31 40 11

External dimensions: **313 x 404 x 111 mm**

Weight: **6400 g**

[illegible]

Maximum number of cable glands <i>to DIN 50262*</i>							
A C D B							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	105	68	7	17.25	103	68
16	25.30	50	28	9	21.85	64	42
20	27.60	39	26	11	25.30	46	27
25	37.95	20	12	13.5	27.60	39	24
32	48.30	14	7	16	31.05	33	18
40	60.95	6	4	21	37.95	18	12
50	69.00	5	3	29	48.30	13	7
63	74.75	5	3	36	60.95	6	4
				42	69.00	5	3
				48	74.75	5	3




* Please quote mounting side

Type: **01.31 40 14**External dimensions: **312 x 403 x 141 mm**Weight: **9500 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
381	360	26	2	•	•	•	•	•	•	•	•	•	•

Maximum number of cable glands to DIN 50262*							
							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	147	95	7	17.25	147	95
16	25.30	70	43	9	21.85	96	55
20	27.60	55	32	11	25.30	70	40
25	37.95	28	18	13.5	27.60	55	32
32	48.30	17	10	16	31.05	44	28
40	60.95	12	7	21	37.95	27	18
50	69.00	7	4	29	48.30	17	10
63	74.75	6	3	36	60.95	12	7
				42	69.00	7	4
				48	74.75	6	3



Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688

Cylinder screw
M6x25/10
similar to DIN 84


Base

Type: **01.31 40 18**External dimensions: **313 x 404 x 181 mm**Weight: **9780 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
381	360	26	2	•	•	•	•	•	•	•	•	•	•



Maximum number of cable glands to DIN 50262*							
							
M	Corner dim.	Side		PG	Corner dim.	Side	
		A	C			A	C
12	17.25	205	122	7	17.25	205	122
16	25.30	98	54	9	21.85	128	77
20	27.60	78	51	11	25.30	98	54
25	37.95	40	24	13.5	27.60	75	48
32	48.30	22	15	16	31.05	60	38
40	60.95	15	9	21	37.95	38	24
50	69.00	11	6	29	48.30	22	15
63	74.75	8	6	36	60.95	14	8
				42	69.00	10	6
				48	74.75	10	6

Lid



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688


Cylinder screw
M6x25/10
similar to DIN 84



* Please quote mounting side

Type: **01.31 40 23**External dimensions: **313 x 404 x 227 mm**Weight: **11000 g**


DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
381	360	26	2	•	•	•	•	•	•	•	•	•	•



Maximum number of cable glands to DIN 50262*									
M	Corner dim.	Side		PG	Corner dim.	Side			
		A	C			A	C		
12	17.25	246	162	7	17.25	246	162		
16	25.30	126	72	9	21.85	160	99		
20	27.60	100	68	11	25.30	112	72		
25	37.95	54	33	13.5	27.60	100	64		
32	48.30	30	20	16	31.05	77	53		
40	60.95	18	12	21	37.95	54	33		
50	69.00	15	9	29	48.30	30	20		
63	74.75	12	8	36	60.95	18	12		
				42	69.00	15	9		
				48	74.75	14	8		

Type: **01.31 60 11**External dimensions: **310 x 600 x 111 mm**Weight: **10160 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
581	560	41	2	•	•	•	•	•	•	•	•	•	•



Maximum number of cable glands to DIN 50262*									
M	Corner dim.	Side		PG	Corner dim.	Side			
		A	C			A	C		
12	17.25	150	68	7	17.25	150	68		
16	25.30	76	28	9	21.85	96	42		
20	27.60	60	24	11	25.30	72	27		
25	37.95	30	12	13.5	27.60	60	24		
32	48.30	20	7	16	31.05	48	18		
40	60.95	10	4	21	37.95	28	12		
50	69.00	8	3	29	48.30	20	6		
63	74.75	6	3	36	60.95	10	4		
				42	69.00	8	3		
				48	74.75	6	3		


* Please quote mounting side

Weight: **12560 g**

Maximum number of
cable glands **to DIN 50262***





The diagram shows a cross-section of a cable gland assembly. A central rectangular block is labeled 'B' below it. To the left of this block is a circular component labeled 'C'. To the right of the central block is a rectangular component labeled 'D'. Above the central block is a label 'A'.




* Please quote mounting side

Type: **01.60 60 20**External dimensions: **600 x 600 x 202 mm**Weight: **26200 g**

DIN rail length in mm	max. fitting length in mm	Earthing rail clamp	Mounting plate (thickness in mm)	External mounting brackets	External hinge* set	EMC version	Internal hinge* set	SWB / SBG / SBGL Corr.protection	Allen lid screws	Silicone lid seal	Sealable lid screws in steel	Turn bolt fastener on request	Quick lock
TS 35													
575	552		2.5		•			•		•			

Maximum number of cable glands to **DIN 50262***

* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



M	Corner dim.	Side		PG	Corner dim.	Side	
		A	B			A	B
12	17.25	270	270	7	17.25	270	270
16	25.30	140	140	9	21.85	184	184
20	27.60	108	108	11	25.30	134	134
25	37.95	56	56	13.5	27.60	108	108
32	48.30	32	32	16	31.05	84	84
40	60.95	22	22	21	37.95	56	56
50	69.00	16	16	29	48.30	32	32
63	74.75	12	12	36	60.95	18	18
				42	69.00	12	12
				48	74.75	12	12

* Please quote mounting side