



FEATURES:

- Connector meets the interface requirements of MIL-STD-348

MATERIALS:

Body and Fittings – Brass, Tarnish Resistant Plating

Center Contact – Gold Plated Beryllium Copper

Dielectric: PTFE

Marking: "Pomona 4160"

RATINGS:

Operating Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: -65°C to +165°C

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 4160

Parts are packaged one per bag, unassembled.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA