



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
6832	5.0	.060	.050	0.63	100,000	C-2R
6152	5.0	.060	.150	1.89	5,000	C-2R
7132	5.0	.075	.090	1.13	25,000	C-2R
7152	5.0	.115	.150	1.89	40,000	C-2R

NOTES:

1. GLASS ENVELOPE TO BE OF TIPLESS AND SEAMLESS CONSTRUCTION TO PROVIDE UNDISTORTED END VIEWING.
2. WIRE TERMINALS TO BE TINNED DUMENT TYPE WIRE. OPTIONAL PLATING MATERIALS ARE AVAILABLE.
3. ALL LAMPS TO BE 100% AGED FOR AN EQUIVALENT OF TEN HOURS OF THE RATED VOLTAGES.
4. FINAL INSPECTION ON ALL LAMPS TO BE MIL. STD. 105-E. ELECTRICAL CHARACTERISTICS TO AN AQL OF 2.5 OR BETTER, LEVEL II. MECHANICAL TO AN AQL OF 4.0, LEVEL S-1. (NOTE: AS15 TYPE LAMPS WILL BE 100% INSPECTED FOR AMPERAGE AND MSCP RATINGS.)
5. ALL DIMENSIONS PROVIDED HEREIN, NOT LISTING TOLERANCES, ARE CONSIDERED REFERENCE DIMENSIONS ONLY.

METRIC THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE T-1 SHORTY WIRE TERMINAL LAMP	
C DIM. CHNG. 0.8±0.13 TO 0.8 REF. B LEAD DIA. 0.25 TO 0.25 REF. A DRAWING TO CAD - LAMPS 2022, 6802 DELETED RELEASED	5/21/01 02/08/00 01/14/00 07/07/97	DRAWN BY L. WENGSTROM	APPV'D BY QC	DATE 5/21/01	SIZE A
DESCRIPTION/ECO NUMBER		APPV'D DATE		SCALE NONE	
REV. NO.		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		FSCM NO. 55335	
REV. NO.		RELEASED DATE		DRAWING NO. WIRE TERMINAL SHORTY T-1	
REV. NO.		RELEASED DATE		REVISION DATE 5/21/01	
REV. NO.		REV. NO.		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[6832](#) [7132](#) [6152](#)