ED120/XDS



2-12 poles, Spacing 5.08 mm
insert required no. of poles **x**
How to order see page 5

Ratings:		
Rated Voltage	**300 V**	**250 V**
Rated Current	**15 A**	**24 A (T60)**
Wire Size	**AWG 22-14**	**2.5 mm²**
Test Voltage		**2.0 kV**
Rated Torque/ScrewSize		**0.5 Nm/M3**
Max. Rated Cross Section		
Single Wire (solid)		**2.5 mm²**
Stranded Wire (flexible)		**1.5 mm²**
Stranded wire with Ferrules		**1.5 mm²**
Dimensions		
Spacing		**5.08 mm**
PCB Hole Diameter		**1.3 mm**
Stripped Length		**7.0 mm**
Materials		
Insulating Material		**PA**
Flammability Class		**UL94 V-0**
Temperature Range		**-30˚C/+105˚C**
Terminal Block		**CuZn**
Wire Guard		**Stainless Steel**
Color		
Blue