

[United States \[Change\]](#) | [Fluke \[Change\]](#)**FLUKE**[Home](#) | [Products](#) | [Accessories](#) | [Current Clamps](#) |[Contact us](#)

i200s AC Current Clamp

Available
inventoryFluke
storeDownload
manuals

Search Fluke

☒ Resources ☐ Products

Find Resources

[Overview](#) | [Features](#) | [Specifications](#) | [Models and Accessories](#) | [Knowledge and Information](#)

Specifications	
Nominal current range	20 A 200 A
Continuous current range	0.1 A – 24 A 0.5 A – 200 A
Maximum Non-Destructive Current	240 A
Lowest measurable current	0.1 A
Basic Accuracy	1.5% + 0.5 A (48–65 Hz) (% reading + floorspec)
Useable frequency	40 Hz – 10 kHz
Output level(s)	100 mV/A 10 mV/A

Safety Specifications	
Safety	CAT III, 600 V
Maximum voltage	600 V AC

Mechanical & General Specifications	
Warranty	1 year
Maximum conductor diameter	20 mm
Maximum conductor size (busbar)	20 x 5 mm
Output cable length	2.0 m
BNC Adapter	Yes
BNC to banana adapter included	Yes

