




1. MARKED PER MIL-STD-130.
2. LEADS WILL MATE WITH AMP LGH-3 RECEPTACLE WITH 1.81 [46.0] BARREL DEPTH.
3. PIGTAIL IS SOLDER DIPPED.
4. OPERATING VOLTAGE: 40 KVDC AT 0 TO 70,000 FEET, -55°C TO 125°C.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± .02 [0.5] 3 PLC DEC ± - ANGLES ± -	DR 1-21-98 C.C.THOMAS	AMP AMP Incorporated Harrisburg, PA 17105-3608		
SEE CALLOUTS	CHK 1-21-98 D.EABY			
FINISH	RLSE 1-21-98 C.C.THOMAS	NAME LEAD ASSY, SGL END, LGH-3 WIRE COLOR: RED		
SEE CALLOUTS	PRODUCT SPEC -			
	APPLICATION SPEC -	SIZE C	CAGE CODE 00779	DRAWING NO C-1218110
	WEIGHT -	SCALE 2:1	SHEET 1 OF 1	