

Double Row Terminal Blocks

600 Volts AC/DC (Classes B/C)



Specifications:

- Base, Thermoplastic, 125°C (UL RTI)
- Closed Back Design
- Screws, #6-32 Binder Head, Phil-Slot, Steel
- Terminals, Plated Brass
- 1-30 Poles
- 7/16" Centers
- Wire Range With Wire Binding Screw
#12 - #22 AWG – 20 Amps
- Wire Range With Sems Pressure Screw #12 - #22 AWG
Stranded Copper Wire Only, 20 Amps
- UL Recognized File No. XCFR2.E62806
- CSA Certified File No. LR19766
- 
- RoHS Compliant

Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

CATALOG #	PRODUCT DESCRIPTION	PAGE REFERENCE
MSP	KULKA	
	KT37	Full Quick Connect (0° Flat)
	KT38	Full Quick Connect (45° Bend)
	KT39	Full Quick Connect (90° Bend)
	KT43	Half Quick Connect (0° Flat)
	KT44	Half Quick Connect (45° Bend)
	KT45	Half Quick Connect (90° Bend)
	ST	Full Solder
	3/4 ST	Half Solder
	J 621	Line to Line Jumper
	601RJ(S)	Multiple Position Jumper
	3765	SEMS Pressure Saddle Screw
	3767	SEMS Pressure Saddle Screw
		with External Tooth Lock Washer
PSB		Phil-Slot Brass Screw

PSB

Quick Connects: .032" x .250"

See pages 104-115 for terminal block accessories

$$\text{mm} = \text{dim} \times 25.4$$

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html