



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PMS*** - SNAP-ON PIPEMARKERS						
PART NUMBER	LENGTH "A" +/- .062	WIDTH "B" +/- .062	I.D. "C" +/- .062	PIPE/ CONDUIT OUTSIDE DIA. RANGE	MARKER PER PKG.	STD. PKG. QTY.
PMSCLL	3.0 [76.0]	4.0 [102.0]	0.44 [11.2]	0.50 [13.0]-0.75 [19.0]	5	1
PMSCLP	13.0 [330.0]	8.0 [203.2]	1.125 [28.6]	0.75 [19.0]-2.25 [57.0]	5	1
PMSCLN	17.0 [431.8]	12.0 [304.8]	1.5 [38.1]	2.25 [57.0]-3.25 [83.0]	5	1
PMSCLM	17.0 [432.0]	23.0 [585.5]	2.0 [50.8]	3.25 [83.0]-6.00 [152.0]	5	1

NOTE:
1. MILLIMETERS ARE IN ().



										CAD FILENAME/LAYERS		I00318BF-DC-C10943/01A	
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										CUSTOMER DRAWING PRE-COILED CLEAR SNAP-ON PIPEMARKER			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY RVU	MAT'L: CLEAR POLYESTER GMPET GMSTRIP GMY6		SCALE NTS
0	9/23/11	RVU		DRAWING RELEASE			6522	R		DATE 9/27/11	DRAWING NO. C10943		DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST	SUP		