




ORDERING INFORMATION

92316-****

CIRCUIT SIZE —
LENGTH L IN CENTIMETRES

LENGTHS AVAILABLE FROM 6 CM TO 120 CM

e.g. 92316-1208 = 12 CIRCUIT
WITH LENGTH L OF 8 CM.

NOTE : FOR LENGTHS OF

100 CM , THE PART NO. IS 92316-**01

105 CM , THE PART NO. IS 92316-**02

110 CM , THE PART NO. IS 92316-**03

115 CM , THE PART NO. IS 92316-**04

120 CM , THE PART NO. IS 92316-**05

90327 CONNECTOR	
CIRCUIT SIZE	DIMENSION W
4	7.59
6	10.13
8	12.67
10	15.21
12	17.75
14	20.29
16	22.83
18	25.37
20	27.91
22	30.45
24	32.99
26	35.53

90584 CONNECTOR	
CIRCUIT SIZE	DIMENSION W
4	7.59
6	10.13
8	12.67
10	15.21
12	17.75
14	20.29
16	22.83
18	25.37
20	27.91
22	30.45
24	32.99
26	35.53

CABLE DETAILS:

28 AWG , 1.27 MM PITCH , 7 STRANDS WITH TINNED COPPER ,
GREY PVC INSULATION WITH A COLOURED POLARITY STRIPE
INDICATING CIRCUIT NO. 1, UL 2651.

NOTES:

1. SEE PRODUCT SPECIFICATIONS PS-99020-0011.
2. SEE TERMINATION SPECIFICATION ES-99033-0001.
3. SEE TERMINATION SPECIFICATION ES-99033-0002.
4. SEE CABLE SPECIFICATION ES-99027-0006.
5. HARNESSES WILL BE 100% ELECTRICALLY TESTED FOR SHORTS AND DISCONTINUITIES.

REF DIM ADDED EC NO. 2003-0374 DRAWN: P.FINN 02/02/11 CHK'd: / / APP'r: / /	DESCRIPTION	QUALITY SYMBOLS MAJOR = CRITICAL =	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 4 : 1	DESIGN UNITS ☒ mm ☐ INCH		THIRD ANGLE PROJECTION	DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY		SHT	REV
					mm	INCH	DRAWN BY & DATE MCURRAN 98/06/19		TITLE: PICO FLEX IDT TO BOARD-IN STANDARD ASSEMBLIES			
			4 PLACES	±0.	±.	CHECKED BY & DATE AMcCANN 98/06/19						
			3 PLACES	±0.	±.	APPROVED BY & DATE MWILHITE 98/06/19		MOLEX INCORPORATED				
			2 PLACES	±0.	±.	CAD FILENAME	MATERIAL NO.	DRAWING NO.	SHEET NO.			
			1 PLACE	±0.	±.	S92316X1.DGN	SEE CHART	SD-92316-001	1 OF 1			
			ANGULAR: ± 1/2 °									
REV			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.							SIZE B