


171505



1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

(P/N)	(STUD)	(H DIM)	(INS. DIA)
型番	ストッド	H寸法	被覆外径
171505-1	#4	3.02	2.03~3.18
-2	#6	3.68	2.03~3.18
-3	#4	3.02	2.67~3.56
-4	#6	3.68	2.67~3.56
-5	#1	2.03	2.03~3.18
-6	"	3.25	2.03~3.18
171505-7	#2	2.36	2.03~3.18

OBSOLETE 1

D2	REV PER ECO-10-000444	KK	AEG	08 JAN 10
D1	OBSOLETE (REV. B) K.N. 4T			
D	REVISED (REV. B) K.Y. 4T			
C	REVISED (REV. B) S.O. 4T			
B	ADDED MARK H.S. 4T			
A	REVISED (REV. A) H.S. 4T			
LTR	変更 REVISION RECORD	DR	CHK	DATE

(C) 1975 AMP (JAPAN) LTD. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.
 参考図面 (CUSTOMER COPY REFERENCE ONLY)
 AMP (JAPAN) LTD. Tokyo, Japan
 電気銅 銅めっき
 WIRE RANGE 0.26~1.04 (AWG 22-18)
 (TOLERANCE) ±0.5 (EXCEPT AS NOTED) ±1.0
 4-1 JAC-171505
 丸型端子 RING TERMINAL

参考図面 (CUSTOMER COPY REFERENCE ONLY)
 AMP (JAPAN) LTD. Tokyo, Japan
 丸型端子 RING TERMINAL
 4-1 JAC-171505
 丸型端子 RING TERMINAL