



Current refinements (click to remove)

[Search Tips](#)

☐ Region USA ☐ Product Family HLM / HLS Hook & Loop Strips and Rolls

Text Search: 'HLS5SX2'

Your search criteria matched only one product, shown below.

Related Products

[Click here to see image](#)

- Strip Ties (HLS) Rolls performed in convenient 6", 12" and 18" strips
- 15' & 75' Rolls (HLM/HLS 15 & 75)- Can be cut to desired length, eliminating waste
- Adjustable, releasable, and reusable hundreds of times for applications requiring frequent moves, adds, or changes
- Hook and loop material maintains network data integrity protecting against over-tensioning of high performance copper and fiber cables
- Easy to use and operator safe with no sharp edges
- Complementary mounts available

- [Tak-Ty Hook & Loop Cable Tie Mounts](#)
- [Tak-Ty Hook & Loop Cable Tie Mounts](#)
- [4-Way Adhesive Backed Cable Tie Mounts](#)
- [Flat Pan-Post™ Standoff Mounts](#)
- [Extra-Heavy Cable Tie Mounts](#)
- [Swivel Mounts](#)
- [More...](#)

Note: Minimum 2" overlap required to achieve loop tension

Part Number:	HLS5SX2
RoHS Compliancy Status:	Compliant
Part Description:	Hook & Loop Cable Tie, Strips, 18.0", Standard (1/2") section
Product Type:	Cable Ties
Material:	Nylon Loop, Polyethylene Hook
Color:	Red
CSA Certified:	No
UL Listed (File #E56854):	No
UL Recognized (File #E56854)	No
Length (In.):	18.0
Length (mm):	457
Width (In.):	.750
Width (mm):	19.1
CE Compliant:	Yes
Cross Section:	Standard
Locking Style:	Hook & Loop
Max. Bundle Diameter (In.):	5.00
Max. Bundle Diameter (mm):	127
Min. Loop Tensile Strength (L 50)	
Min. Loop Tensile Strength (N 222)	
Temperature Range:	0°F to 220°F
Thickness (In.):	.10
Thickness (mm):	2.5
Min. Order UOM:	PC
Min. Order Qty.:	10
BOM Qty. (# of Pkgs.)	0

Add to My Catalog

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.