

HC-M-KV-M40(27-34)

Order No.: 1607729

The illustration shows version HC-M-KV-M20



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1607729>

Metal screw connection up to 5 bar, thread length: 8 mm, cable
diameter: 27 ... 34 mm, WAF 50, screw connection: M40

Commercial data

GTIN (EAN)	 4 017918 938819
sales group	D290
Pack	10 pcs.
Customs tariff	74199990
Catalog page information	Page 521 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
06/07/2006



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

General data

Type of the screw connection	M40
Cable gland material	Nickel-plated brass
Seal material	Neoprene
Cable seal material	Neoprene
Material, O-ring	NBR

Wrench size, union nut	50 mm
Wrench size, support	50 mm
Thread type connection side 1	M40
Length of the connecting thread	8.00 mm
External cable diameter	27 mm ... 34 mm
Conductor sealing range	27.00 mm ... 34.00 mm
Tightening torque, union nut	20.00 Nm
Degree of protection	IP68, to 5 bar
Ambient temperature (operation)	-20 °C ... 100 °C

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;