










MATING CONNECTOR INTERFACE



TYPICAL RECEPTACLE CAVITY SECTION
(DIMENSIONS REFERENCE ONLY)



RECOMMENDED CUT OUT
FOR 1.52 MAX THICK PANEL



3-DIMENSIONAL MODEL
NTS

2.13	.084	6.73	.265	-	-
1.57	.062	5.08	.200	25.53	1.005
1.52	.060	5.05	.199	19.69	.775
0.38	.015	3.68	.145	16.51	.650
0.25	.010	3.18	.125	12.50	.492
0.13	.005	2.67	.105	12.45	.490
MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN MM (INCHES) TOLERANCES ON: 2 PLC DEC ± 0.13 3 PLC DEC ± 0.13 ANGLES ± 1°		DR 11-4-93 K. WHITAKER	770326-1 PART NO		
MATERIAL NYLON, UL 94V-2 NATURAL	FINISH -	CHK 11-4-93 R. SMITH	AMP AMP Incorporated Harrisburg, PA 17105-3508		
		APPD 11-4-93 C. CASH	NAME RECEPTACLE, PANEL MOUNT, 3 CIRCUIT, .062 PIN AND SOCKET		
PRODUCT SPEC -	APPLICATION SPEC -	APPD 11-4-93 C. CASH	SIZE D	CAGE CODE 00779	DRAWING NO C-770326
		WEIGHT -	SCALE 5:1	SHEET 1 OF 1	

CUSTOMER DRAWING