







Hybrid Han 3A - LC Duplex and Power AC, with metal housing

Hybrid cable
FO 2xG50/125 + POWER 3x2.5/3.5



Loading-Plan



9	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 300 5001	300 (±3.00)m
8	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 100 5001	100 (±1.00)m
7	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 060 5001	60 (±0.60)m
6	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 050 5001	50 (±0.50)m
5	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 040 5001	40 (±0.40)m
4	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 020 5001	20 (±0.20)m
3	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 010 5001	10 (±0.10)m
2	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 005 5001	5 (±0.05)m
1	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 001 5001	1 (±0.01)m

Cont No.	Type of cable	Part-No.	Dim. a
----------	---------------	----------	--------

 All Dimensions in mm Original Size DIN A 3	Techn. Character.			Nicht tolerierte Maße/	
				Hybrid cable assembly, FO 2xG50/125 + POWER 3x2.5mm ² , 1xHAN3A, LC duplex MM, 3xpower AC	
DRS491A	22.04.09	MR	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP		TB 33 57 111 xxx 5001
S468A					
Mod.	Dat.	Name			Blatt/ page

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[33571110015001](#) [33571110055001](#) [33571110105001](#) [33571110205001](#) [33571110405001](#) [33571110505001](#)
[33571111005001](#)