







|           |                                     |          |                                         |           |          |
|-----------|-------------------------------------|----------|-----------------------------------------|-----------|----------|
| PART NAME | NEMA 4X DIE CAST ALUMINUM ENCLOSURE | PART No. | AN-1313, AN-1313-G, AN-2813 & AN-2813-B | REV. DATE | 12-17-08 |
|-----------|-------------------------------------|----------|-----------------------------------------|-----------|----------|



$\varnothing 0.125 \times 0.500$  DEEP (1x)  
 ACCEPTS M3.5 x 6mm  
 SELF-TAPPING SCREW  
 (NOT SUPPLIED)



MATERIAL: ALUMINUM ALLOY #ADC-12


FINISH: NATURAL (NO SUFFIX)

GRAY (SUFFIX -G)

SMOOTH BLACK (SUFFIX -B)

NOTES:

- 1) FOUR (4) M4 x 25mm (0.975") LG. SCREWS SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE  $\pm 0.005$  TOLERANCE. ALL OTHER DIMENSIONS HAVE  $\pm 0.015$  TOLERANCE.



PART NO. AN-2813 & AN-2813-B  
 ARE SUPPLIED WITH A WELDED  
 ON MOUNTING BRACKET ONLY.