



DCH213M2

18 Volt Lithium Ion Heavy Duty 3 Mode Dedicated Cordless Hammer

Selling Proposition

- Ideal for drilling anchors and fixing holes into concrete, brick and masonry from 4mm to 20mm
- Rotation stop mode for light chiselling in plaster, tiles and render and impact stop mode for rotary only drilling in wood and metal
- New 4.0Ah 18 Volt Lithium Ion battery, delivers high performance, long life and maximum runtime
- Best in class vibration, 6.9m/s² reduces user fatigue and maximises operating periods
- Bright white LED with delay feature improves visibility

Standard Equipment

- 2 x 4.0Ah batteries
- XR multi-voltage charger
- multi-position side handle
- heavy duty carrying case

Warranty Specifications

- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract
- 1 Year Warranty

Specifications	
Voltage	18 V
Battery Capacity	Li-Ion 4.0 Ah
Power Output	300 Watts
No Load Speed	0-1100 rpm
Impact energy (EPTA 05/2009)	2.0 J
Blows per Minute	0-4200 bpm
Tool Holder	SDS-Plus
Max. Drilling Capacity [Wood]	26 mm