


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	MILITARY PART # AND CLASS	STUD SIZE		DIMENSIONS in. [mm]				
		ENGLISH	METRIC	L ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M ± .03 [0,8]	H ± .01 [0,3]
PN14-4R	MS25036-152 CLASS 2	#4	M3	.76 [19,3]	.25 [6,4]	.22 [5,6]	.65 [16,5]	.12 [3,1]
PMN2-3R	-----	--	M3	.85 [21,6]	.23 [5,8]	.20 [5,1]	.65 [16,5]	.13 [3,3]
PN14-6R	MS25036-107 CLASS 2	#6	M3,5	.86 [21,8]	.31 [7,9]	.25 [6,4]	.70 [17,8]	.15 [3,8]
PN14-6RN	MS25036-106 CLASS 2	#6	M3,5	.76 [19,3]	.25 [6,4]	.22 [5,6]	.65 [16,5]	.15 [3,8]
PN14-8R	MS25036-153 CLASS 2	#8	M4	.86 [21,8]	.31 [7,9]	.25 [6,4]	.70 [17,8]	.17 [4,3]
PN14-10R	MS25036-108 CLASS 2	#10	--	.86 [21,8]	.31 [7,9]	.25 [6,4]	.70 [17,8]	.20 [5,1]
PMN2-5R	-----	--	M5	.97 [24,6]	.35 [8,9]	.26 [6,5]	.71 [18,0]	.21 [5,3]
PN14-14R	MS25036-154 CLASS 2	1/4"	M6	1.06 [26,9]	.44 [11,2]	.38 [9,7]	.83 [21,1]	.27 [6,9]

NOTES:


- USED FOR:
 - #16-14 AWG [1,5-2,5 mm²] SOLID OR STRANDED COPPER WIRE
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
 - 600 V. MAX. VOLTAGE RATING
- INSTALLATION TOOLS:
 - PRESSES: CP-861, CP-862, CP-871
 - APPLICATOR: CA-800EZ, CA9
 - DIE INSERTS: CD-800-2, CD9-2A, CD9-2B
- WIRE STRIP LENGTH: 1/4 ^{+1/32}₋₀ [6,4^{+0,8}₋₀]
- MATERIAL:
 - STAMPING: .03" [0,8] THK COPPER, TIN PLATED
 - HOUSING: NYLON, BLUE
 - SLEEVE: BRASS, TIN PLATED
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT




LISTED
587H
E52164



CERTIFIED
LR31212



										TITLE				
										RING TERMINALS, 3 PC. NYLON INSULATED, #16-14				
										CUSTOMER DRAWING				
										ITEM REVISION NAME		N41099BA/07		PANDUIT
										DATASET FILE NAME		N41099BA_DC/07A		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.13] .xx ± .01 [.25] ANGLES ± 5 °				
										THIRD ANGLE PROJECTION				
07	09.12.12	JBN	LCA	VMB	ADDED METRIC EQUIVALENT. REVISED NOTES. UPDATED DRAWING TO CURRENT STANDARDS.	A41099					MATERIAL:		SEE NOTES	
											DRAWING NUMBER:		A41099	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE	
							JMV	-	LA	N.T.S.			A	