




Dimensions mm and (In.)

Specifications:

- Insertion and extraction force: 0.3 Kgs. to 3.0 Kgs.
- Withstand voltage test: 250 VAC 50 to 60Hz for 1 min.
- Insulation resistance: 100M Ω min 250 VDC
- Contact resistance: 50m Ω Max
- Durability test: 5000 mating cycles
- Operating temperature: -25 to 85°C
- Rated voltage: 16 volts DC
- Rated current: 0.3 ampere
- Plastic housing: LCP, Black UL94V-0 rated
- Contacts: Brass, Gold flash Plated

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-4025](#)