


Model 2894 Binding Post To Single Banana Plug



FEATURES:

- Features insulated binding post for rapid mounting and interchangeability of components.
- Center cross hole 4.2 (.166) dia. Provides side stackup connection.

MATERIALS:

Upper Conn.: Binding Post – Insulated

Material: Binding Post Body – Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 micro-inches.

Insulation: Polycarbonate. Color: See Ordering Information.

Insulation: ABS molded to binding post and banana plug body. Color: Black.

Marking: “2894 POMONA ELECTRONICS CALIF.”

Lower Conn.: Banana Plug

Material: Spring – Beryllium Copper per QQ-C-533, Alloy 172, Cond. Plug Body – Brass per QQ-B-626, Alloy 360, ½ Hard

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 micro-inches.

RATINGS:

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: 2500 VDC

Current: 15 Amperes

ORDERING INFORMATION: Model 2894-*

*=Color, -0 Black, -2 Red

Ordering Example: 2894-2 Color is Red.

Other colors available on special request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[2894-2](#) [2894-0](#)