


Deep groove ball bearings, single row, shield on both sides



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN	C_0	kN	r/min		kg	-
9	24	7	3,9	1,66	0,071	70000	34000	0,014	609-2Z *



Calculation factors

k_r 0,025
 f_0 13