



Features

- Intel® Core™ i7 Processor, 2.53 GHz max.
- Up to 8GB DDR3 ECC RAM with rugged small outline memory module (RSOMM)
- 2 DisplayPorts, LVDS (dual channel)
- 2x Gigabit Ethernet
- 10x USB 2.0 host ports, 2x with extended power capability
- 4x SATA with RAID support
- Supports Smart Embedded Management Agent (SEMA) functions

Specifications

Core System

Processor	Intel® Core™ i7 processor Intel® Core™ i7 – 620UE, 1.06 GHz, dual core Intel® Core™ i7 – 610E, 2.53 GHz, dual core
RAM	8 GB DDR3 ECC RAM maximum 4GB soldered 4GB RSOMM module (optional)
RAM Clock	DDR3 1066MHz
Chipset	Mobile Intel® QM57 Express Chipset
BIOS	Phoenix BIOS BIOS parameters are saved in flash
Watchdog	Yes (SEMA)
SEMA	Yes, Condition Monitoring
PCI Express Bus	PCIe/104 Type 1 connector with - 4 x1 lanes (PCIe 1.0a) - 1 x16 lane, configurable as 2 x8 lanes (2.5Gbit/s, PCIe 2.0 compliant)
PCI Bus	PCI-104
LPC Bus	Yes
SPI Bus	Yes
SMB Bus	Yes

Video

LVDS	Dual channel 18/24-bit LVDS, resolution up to 1920 x 1200 @ 60Hz
------	--

Audio

Optical SPDIF
Analog 7.1 (Azalia)

Power

Power Supply	ATX 1.3 compatible
Power Consumption	25 to 45 watts, depending on processor type
RTC Backup	Integrated battery

Multi I/O and Storage

USB	6x USB 2.0 host external access, 2x supporting up to 1A max. 4x USB 2.0 host internal only
-----	---

Ethernet


2 x Gigabit Ethernet	- Integrated in chipset, with 82577 PHY - Intel® 82574
SATA	4 ports, support for RAID 0, 1, 5, 10

Mechanical and Environmental

Board Format	115 x 165mm
Cooling	Passive cooling possible Heatspreader available
Operating Temperature	Standard: 0°C to 60°C Industrial: -20°C to 60°C Extended: -40°C to 85°C (optional)
Shock & Vibration	VITA 47-2005 V3 & OS tests approved
Status LED	HDD, power, power mode, SMC activity, 4x Ethernet, watchdog
MTBF	128,820 hours at 25 °C

Operating Systems

Standard Support	Windows, Linux
------------------	----------------



 3. 4. 5. 6. 7. 8. 9. 10. 11. 12. 13. 14. 15. 16. 17. 18. 19. 20. 21. 22. 23. 24. 25. 26. 27. 28. 29. 30. 31. 32. 33. 34. 35. 36. 37. 38. 39. 40. 41. 42. 43. 44. 45. 46. 47. 48. 49. 50. 51. 52. 53. 54. 55. 56. 57. 58. 59. 60. 61. 62. 63. 64. 65. 66. 67. 68. 69. 70. 71. 72. 73. 74. 75. 76. 77. 78. 79. 80. 81. 82. 83. 84. 85. 86. 87. 88. 89. 90. 91. 92. 93. 94. 95. 96. 97. 98. 99. 100.

| Model Number | Description/Configuration |
|--------------|--|
| 714-0006-10 | EPIC-Express, Hurricane-QM57, Intel i7-620UE,
1.06 GHz, 2GB RAM, 0°C to +60°C |
| 814-0006-10 | EPIC-Express, Hurricane-QM57, Intel i7-620UE,
1.06 GHz, 2GB RAM, -20°C to +60°C |
| 914-0006-10 | EPIC-Express, Hurricane-QM57, Intel i7-620UE,
1.06 GHz, 2GB RAM, -40°C to +85°C |
| 714-0007-10 | EPIC-Express, Hurricane-QM57, Intel i7-610E,
2.53 GHz, 2GB RAM, 0°C to +60°C |
| 814-0007-10 | EPIC-Express, Hurricane-QM57, Intel i7-610E,
2.53 GHz, 2GB RAM, -20°C to +60°C |
| 914-0007-10 | EPIC-Express, Hurricane-QM57, Intel i7-610E,
2.53 GHz, 2GB RAM, -40°C to +85°C |
| 714-0008-10 | EPIC-Express, Hurricane-QM57, Intel i7-610E,
2.53 GHz, 2GB RAM, -40°C to +85°C |
| 814-0008-10 | EPIC-Express, Hurricane-QM57, Intel i7-610E,
2.53 GHz, 4GB RAM, -20°C to +60°C |
| 914-0008-10 | EPIC-Express, Hurricane-QM57, Intel i7-610E,
2.53 GHz, 4GB RAM, -40°C to +85°C |

| Year | Percentage |
|------|------------|
| 1990 | 85 |
| 1992 | 65 |
| 1994 | 65 |
| 1996 | 65 |
| 1998 | 65 |
| 2000 | 65 |
| 2002 | 65 |
| 2004 | 65 |
| 2006 | 65 |
| 2008 | 65 |
| 2010 | 65 |

| Model Number | Description/Configuration |
|--------------|---|
| 760-0027-10 | RAM, unbuffered ECC, RSOMM Reverse, 2GB, 0°C to +60°C |
| 860-0027-10 | RAM, unbuffered ECC, RSOMM Reverse, 2GB, -20°C to +60°C |
| 960-0027-10 | RAM, unbuffered ECC, RSOMM Reverse, 2GB, -40°C to +85°C |
| 760-0033-10 | RAM, unbuffered ECC, RSOMM Reverse, 4GB, 0°C to +60°C |
| 860-0033-10 | RAM, unbuffered ECC, RSOMM Reverse, 4GB, -20°C to +60°C |
| 960-0033-10 | RAM, unbuffered ECC, RSOMM Reverse, 4GB, -40°C to +85°C |
| 765-0031-10 | Heat Sink, active, Hurricane-QM57 |
| 765-0032-10 | Heat sink, heat pipe adapter, Hurricane-QM57 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ADLINK Technology:

[HUR-QM57-R-610E/4G](#) [HUR-QM57-E-610E/2G](#) [HUR-QM57-C-610E/2G](#) [HUR-QM57-C-620UE/2G](#) [HUR-QM57-R-610E/2G](#) [HUR-QM57-R-620UE/2G](#) [HUR-QM57-E-620UE/2G](#) [HUR-QM57-C-610E/4G](#) [HUR-QM57-E-610E/4G](#)