


25-PIN SHOWN



No. OF PINS	DIMENSIONS			
	A	B	C	D
009	1.213	0.984	0.642	0.492
	30.81	24.99	16.30	12.50
015	1.541	1.312	0.970	0.656
	39.14	33.32	24.65	16.66
025	2.088	1.852	1.512	0.926
	53.04	47.04	38.40	23.52
037	2.729	2.500	2.157	1.250
	69.32	63.50	54.80	31.75

MATERIAL:

SHELL: STEEL, NICKEL PLATED
INSULATOR: UL 94V-O RATED, BLACK, 260° NYLON
CONTACT: BRASS OR PHOSPHOR BRONZE

ELECTRICAL:

CURRENT RATING: 5 AMPS
DIELECTRIC STRENGTH: 1,000VAC rms
INSULATION RESISTANCE: 1,000 MOHMS Min
TEMPERATURE: -55°C TO +105°C
CERTIFICATION: UL RECOGNIZED TO CATEGORY CODE ECBT2

DO NOT SCALE FROM DRAWING

182-YYY-2 1 3 RYY 1

SERIES
No. of POSITIONS
GENDER
2 = FEMALE
TERMINATION
1 = PC MOUNT
SHELL PLATING
3 = NICKEL
HARDWARE OPTIONS
SEE PAGE 2
PLATING OPTIONS
1 = GOLD FLASH
2 = 30u" GOLD

RoHS COMPLIANT

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN: PAM JENKINS

CHECKED:

SCALE: 1 : 1

DWG NO.








DATE: 03-17-05

DATE:

SHEET 1 OF 2

REV 5

182-YYY-213RYY1

	 0.141 ±0.020 METAL SHELL WITH INSIDE GROUND STRAPS	 METAL SHELL	 METAL SHELL FORK BOARD LOCKS
 .120" DIA. HOLE	16	43	N/A
 4-40 FLUSH INSERT	17	45	53 BOARD LOCKS IN HOLE
 4-40 HEX STANDOFF FEMALE SCREWLOCK	18	48	56 BOARD LOCKS IN HOLE
 4-40 ROUND STANDOFF FEMALE SCREWLOCK	N/A	N/A	N/A

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS

DATE:
03-17-05

CHECKED:

DATE:

NorComp

SCALE:
1 : 1

SHEET
2 OF 2

REV
5

DWG NO. 182-YYY-213RYY1

RoHS COMPLIANT