

Brooder and Heat Lamp

2-Conductor Polarized • Type SJTW • 105°C • 300 Volts • Non-UL

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING		NEMA CONFIG.	PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	WATTS					
04127.60.01	2	18	8	Black	125	250	1-15P	12	1.0	12	079407041275

Product Construction:

Conductor:

- 18 AWG stranded bare copper per ASTM B-174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; black
- Voltage rating: 300 volts

Applications:

- Temporary lighting
- Egg hatching

Features:

- 10 1/2" bell shade
- Porcelain socket
- Hanging clamp
- Swivel clamp with protective vinyl sleeve
- Protective bulb guard
- 250-watt bulb maximum



Clamp Light

2-Conductor Polarized • Type SPT-2 • 105°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING		NEMA CONFIG.	PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	WATTS					
04170.60.02	2	18	6	White	125	150	1-15P	12	0.8	10	079407041701

Product Construction:

Conductor:

- 18 AWG stranded bare copper per ASTM B-174

Insulation:

- Premium-grade PVC; white
- Voltage rating: 300 volts

Applications:

- Temporary lighting

Features:

- 8 1/2" bell shade
- Clamp with protective vinyl sleeve
- Adjustable ball joint
- Switch socket

Industry Approvals:

- UL Listed

