



Water-Soluble Wave Solder Tape

5414

Technical Data

Product Description 3M™ Water-Soluble Wave Solder Tape 5414 has a poly-vinyl alcohol backing which is water soluble and a synthetic water soluble adhesive to mask gold fingers on printed circuit boards during wave soldering.

Product Construction	Backing	Adhesive	Liner	Color	Standard Roll Length
	PVA film	Water soluble synthetic	Kraft paper	Hazy, transparent	36 yds. (33 m)

Typical Physical Properties **Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

		ASTM Test Method
Adhesion to Steel:	4 oz./in. width (4.4 N/100 mm)	D-3330
Tensile Strength at Break:	6 lbs./in. width (105.1 N/100 mm)	D-3759
Elongation at Break:	334%	D-3759
Total Tape Thickness:	2.1 mils (0.053 mm)	D-3652

- Features**
- No adhesive residue after removal.
 - Low static upon liner release and when taping board.
 - Moisture barrier packaging plus desiccant.
 - Humidity extremes do not affect tape properties.
 - Easy manual and machine application.

Storage Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 50% R.H. in the original carton.

Shelf Life To obtain best performance, use this product within 12 months from date of manufacture.

3M™ Water-Soluble Wave Solder Tape

5414

Product Use

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy

Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability

Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Business Industrial Adhesives and Tapes Division

3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

Printed in U.S.A.
©3M 70-0709-4456-9 (2001/6/05)