



LOC
CE
DIST
16

CAC Customer Layout Rev: D



Left Side

Connector(s): MT-RJ SECURE (No Pins)
Mode: MM
Housing Color: Yellow
Geom. Spec: 115-1215



Fiber Path

Fiber A - - - - - B
Fiber B - - - - - A


Notes:

- 1 IL tested at 1300nm.
- 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 3 Label 2 will not be present on any cable assembly less than 5 meters long.
- 4 Includes dust caps (not shown on print).


Right Side

Connector(s): SC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

Rev Per EC#		RELEASE		DATE		DIN		APVD	
A		Rev Per EC#		3/9/2009		-		QV	
P		LTR		REVISION RECORD		DATE		DIN	



Restricted To:



DWG		Cable Assy Configurator		MATERIAL		HEAT TREAT	
CHK		Quick-Ship NetConnect		-		-	
APVD		Quick-Ship NetConnect		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
NAME		FO C/A - 2 fiber, 62.5/125, OFNP (Plenum) jacket, MT-RJ SECURE (No Pins) to SC-Duplex					
SCALE		SIZE		DRAWING NO.		SHEET	
NTS		A2		C- 1907836		1 of 3	
						REV	
						A	

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

THIS DRAWING IS A CONTROLLED DOCUMENT.

	USED ON
1	100% of the time
2	75% of the time
3	50% of the time
4	25% of the time
5	Never used

Qty	U of M	Description	Item No.
2	piece	Trace Label	16
2	piece	CONN SUBASSY, MM, SC 1.6MM	15
2	piece	Eyelet/Shrink tube assembly - White	14
2	piece	SC Duplex Clip	13
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
2	piece	2.5mm ferrule cover	11
2	piece	SC Simplex Housing, Beige	10
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	9
AR	meter	2 fiber, 62.5/125, 1.8 mm, Twinzip, Orange, OFNP (Plenum)	8
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	MT-RJ Keyed Connector Housing - Yellow	6
1	piece	CRIMP EYELET, MT-RJ	5
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	4
1	piece	PIN KEEPER, 3.8MM	3
1	piece	SPRING, MT-RJ, 3.8 DESIGN	2
1	piece	DUST COVER, MT-RJ	1

DIN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK Quick-Ship NetConnect		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Quick-Ship NetConnect					
NAME FO CIA - 2 fiber, 62.5/125, OFNP (Plenum) jacket, MT-RJ SECURE (No Pins) to SC-Duplex					
SCALE NTS	SIZE A2	DRAWING NO. C- 1907836		SHEET 2 of 3	REV A

5 Restricted To:

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.
BFC-ND

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code
Trace # - Human Readable
Part Number
Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code
Trace # - Human Readable
Part Number
Country of Origin

This label is used on all lengths on this drawing.

DIMENSIONS:	
meters	

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 P.L.C.	± .
1 P.L.C.	± .
2 P.L.C.	± .
3 P.L.C.	± .
4 P.L.C.	± .

Restricted To:

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT -		
CHK Quick-Ship NetConnect		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Quick-Ship NetConnect					
NAME FO C/A - 2 fiber, 62.5/125, OFNP (Plenum) jacket, MT-RJ SECURE (No Pins) to SC-Duplex					
SCALE NTS	SIZE A2	DRAWING NO C- 1907836		SHEET 3 of 3	REV A

D

C

B

A