

GO

Journeyman I Series

[Product Index](#) > [Journeyman I Series](#) > J228-8

Journeyman I High-Leverage Diagonal-Cutting Pliers

- ⌚ *High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.*
- ⌚ *Short jaws and beveled cutting edges permit close cutting of wire.*
- ⌚ *Induction-hardened cutting knives for long life.*
- ⌚ *Hot-riveted joint ensures smooth action and no handle wobble.*



Pictured: J228-8

Cat. No.	Cutting Knives	Handle Color	Handle Type	Jaw Length	Jaw Thickness	Jaw Width	Overall Length	Weight (lbs.)
J228-8	standard	red/black	Journeyman	13/16" (21)	7/16" (11)	1-3/16" (30)	8-1/8" (206)	.67

All dimensions are in inches and (millimeters) except where indicated.

Download High-Resolution .jpg photo

Download High-Resolution .jpg lineart

Download High-Resolution .eps photo

Download High-Resolution .eps lineart



The downloadable files are compressed in .zip format to save on downloading times.

Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

⚠ WARNINGS: Always wear approved eye protection.

⚠ WARNINGS: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).