




MATERIALS AND FINISHES:

PART NO. 73415-4680/73415-4681
73415-4682/73415-4683
73415-4685

BODY
BRASS
PLATED 50u" MIN COPPER UNDERCOAT
100~200u" NICKEL UNDERCOAT
2u" MIN GOLD PLATING

CENTER CONTACT
BRASS
PLATED 10u" GOLD

OUTER CONTACT
BERYLLIUM COPPER
PLATED 50u" MIN COPPER UNDERCOAT
100~200u" NICKEL UNDERCOAT
2u" MIN GOLD PLATING

INSULATOR
TEFLON

PART NO.73415-4684

BODY
BERYLLIUM COPPER
PLATED TRI METAL

CENTER CONTACT
BERYLLIUM COPPER
PLATED GOLD

OUTER CONTACT
BERYLLIUM COPPER
PLATED GOLD

INSULATOR
TEFLON

WITHSTAND 48HRS SALT SPRAY TEST

NOTE:

1. PART NO.73415-4681 WITHOUT CONTACT PART
2. 73415-4682 WITH CUSTOMER REQUEST PACKAGE
3. PART NO.73415-4683/73415-4684
PACKAGE 500PCS BY BAG

PS-73598-0220	PRODUCT SPECIFICATION
AS-73597-033	ASSEMBLY INSTRUCTION
SPECIFICATION	DESCRIPTION

73415-4687	NON-MAGNETIC	1 PIECE 73415-4684 PER BAG
73415-4686	GENERAL TYPE	1 PIECE 73415-4680 PER BAG
73415-4685	GENERAL TYPE	SPECIFIC LABEL ON OUTER BOX
73415-4684	NON-MAGNETIC	500pcs BY ONE BAG
73415-4683	GENERAL TYPE	500pcs BY ONE BAG
73415-4682	GENERAL TYPE	SEE NOTE 2
73415-4681	GENERAL TYPE	SEE NOTE 1
73415-4680	GENERAL TYPE	1000pcs BY ONE BAG
PART NO.	DESCRIPTION	PACKAGING

CHG: ADDED P/NS
73415-4686 & -4687.
EC NO: URF2007-0254
DRAWN: ARBERTSON 2007/01/04
CHKD: 2007/01/04
APPR: JIM EIMER 2007/01/04
REV DESCRIPTION

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ± ---	± ---
3 PLACES ± ---	± ---
2 PLACES ± ---	± ---
1 PLACE ± ---	± ---
ANGULAR ± 5 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
MM/IN	SCALE
DRAWN BY JOHN	DATE 2004/09/17
CHECKED BY JOHNSON	DATE 2004/09/17
APPROVED BY MISEN	DATE 2004/09/17
MATERIAL NO.	DOCUMENT NO.
SIZE C	SEE TABLE

DESIGN UNITS	THIRD ANGLE PROJECTION
METRIC	☉
SSMCX PLUG, 50 OHM PLUG CABLE TYPE SSMCX-PC	
MOLEX INCORPORATED	
SD-73415-468	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
SHEET NO. 1 OF 1	