



REV.	DATE	DESCRIPTION
A	01/10/04	UPDATE DRAWING FORMAT



Amphenol Connex									
PART DESCRIPTION									
BNC PC MOUNT RECEPT. JACK									
112554									
PART NO.									
SHEET 1 OF 1									
CAD FILE									
C:/112/112554.DWG									
DWG. NO. 112554.DWG									
REV. A									
SIZE A									
SCALE NA									
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.									
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:									
0.5 - 8mm ± 0.20mm									
8 - 30mm ± 0.40mm									
30 - 120mm ± 0.50mm									
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:									
.020 - .315 = ± 0.007"									
.315 - 1.180 = ± 0.015"									
1.180 - 4.724 = ± 0.020"									
DO NOT SCALE DRAWING									
QTY									
FINISH									
MATERIAL									
DESCRIPTION									
1 BODY BRASS NICKEL 1									
2 INSULATOR TEFLON NATURAL 1									
3 CONTACT PIN PHOS. BRONZE GOLD 1									
4 INSULATOR TEFLON NATURAL 1									
5 LOCK RING BRASS NICKEL 1									
6									
7									
8									