

SKINTOP® SLM/ SLRM


Liquid Tight, Non-Metallic Strain Relief Cable Gland with Metric Threads



SKINTOP® SLM/ SLRM is a durable, liquid tight, easy to assemble strain relief cable gland with Metric threads that is universally suited for all types of machinery & equipment, including automation, motion control, process control and robotics.


Application Advantage:

- The heavy duty SKINTOP® design provides great pullout strength and very reliable strain relief
- Superior integrated locking mechanism includes an internal ratchet for vibration proof protection
- Multi-trapezoidal thread requires just one twist to tighten
- Generous high quality neoprene bushing provides a liquid tight and dust proof, hermetic seal
- Economical solution that covers a large clamping range with only 8 sizes



NOTES:

1. Orders of 2000 pieces or more per item will be bulk packaged unless otherwise requested.
2. UL Status: R = Recognized; L = Listed



Technical Data:

	Materials:			Protection:	70 PSI
	Body:	Polyamide		Seal:	IP 68, 5 Bar (Exceeds NEMA 6/ 6P Pressure rating) IP 69K
	Bushing:	CR		Temperature range:	
	Locknuts:	Included		Static:	-40° C to +100° C
	Color:	- Black (RAL 9005)		Dynamic:	-20° C to +100° C
		- UV Resistant			
		- Gray (RAL 7001)			

SKINTOP® SLM: Liquid Tight, Non-Metallic Strain Relief Cable Gland with Metric Threads

Black	Part Number	Gray	Thread Type & Size	UL Status	Clamping Range ØF inches	SW Wrenching Flats inches	C Overall Length inches	D Thread Length inches	Standard Pack Size	Weight 100 pcs. lbs.
S2507	S1507	M-12X1.5	R	0.138 - 0.276	0.591	1.181	.315	100	1.00	
S2509	S1509	M-16X1.5	R	0.177 - 0.394	0.748	1.339	.315	100	1.50	
S2513	S1513	M-20X1.5	L	0.276 - 0.512	0.984	1.457	.354	100	2.50	
S2516	S1516	M-25X1.5	L	0.354 - 0.669	1.181	1.575	.394	50	3.50	
S2521	S1521	M-32X1.5	L	0.433 - 0.827	1.417	1.850	.394	25	6.00	
S2529	S1529	M-40X1.5	L	0.748 - 1.102	1.811	2.047	.394	10	10.50	
S2536	S1536	M-50X1.5	L	1.063 - 1.378	2.165	2.441	.472	5	17.50	
S2542	S1542	M-63X1.5	L	1.339 - 1.772	2.598	2.795	.472	5	25.50	

SKINTOP® SLRM: Liquid Tight, Non-Metallic Strain Relief Cable Gland with Reducer Bushing

Black	Part Number	Gray	Thread Type & Size	UL Status	Clamping Range of inches	SW Wrenching Flats inches	C Overall Length inches	D Thread Length inches	Standard Pack Size	Weight 100 pcs. lbs.
S2607	S1607	M-12X1.5	R	0.039 - 0.197	0.591	1.181	.315	100	1.00	
S2609	S1609	M-16X1.5	R	0.079 - 0.276	0.748	1.339	.315	100	1.50	
S2613	S1613	M-20X1.5	L	0.197 - 0.394	0.984	1.457	.354	100	2.50	
S2616	S1616	M-25X1.5	L	0.236 - 0.512	1.181	1.575	.394	50	3.50	
S2621	S1621	M-32X1.5	L	0.276 - 0.591	1.417	1.850	.394	25	6.00	
S2629	S1629	M-40X1.5	L	0.591 - 0.906	1.811	2.047	.394	10	10.50	
S2636	S1636	M-50X1.5	L	0.866 - 1.142	2.165	2.441	.472	5	17.50	
S2642	S1642	M-63X1.5	L	1.102 - 1.535	2.598	2.795	.472	5	25.50	