



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
▶ 2 mm system
▶ 2 mm safety system
▶ 4 mm system
▶ 4 mm sliding sleeve system
▶ 4 mm safety system
sockets
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ plugs ▶ plugs ▶ MST 3

MST 3

datasheet for MST 3
article number: 973509102



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 973 509-102
description:	2 mm diameter miniature connector, nickel-plated brass pin with solder connection. Flexible, shatter-proof insulated sleeve. For making up connecting leads with a maximum external diameter of 1.9 mm.
typ:	MST 3 blau/blue
system:	2mm system
order number:	973 509-102
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
pin dimensions	2 mm
type of contact:	pin (unsprung)
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	6 A
Please consider derating curve!	
contact resistance:	6 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PVC - P
environmental conditions:	
temperature range:	-25 °C to +60 °C
drawing	
	